

## DVI to VGA High Resolution Cable with RGB Coaxial (DVI-A to HD15 M/M), 6 ft. (1.83 m)

MODEL NUMBER: P556-006



### Description

Tripp Lite's 6-ft. (1.83 m) DVI to VGA cable allows PC users with a standard HD15 connector to connect to LCD Flat Panel Displays, Projectors, and HDTV with DVI-I connectors. Gold plated contacts ensure excellent conductivity, while double shielding (foil and braid) provides maximum EMI/RFI protection. Both the DVI and HD15 connectors are molded and have integral strain relief for long life reliability.

### Features

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Constructed from mini-coax (RGB) and paired video wire construction for superior signal quality
- Gold plated copper contacts ensure excellent conductivity
- DVI-A Male to HD15 Male molded connectors
- PC and Mac compatible
- Meets DVI DDWG Standard
- Supports analog signal only

## Specifications

OVERVIEW	
UPC Code	037332120724
Technology	DVI; VGA/SVGA
PHYSICAL	
Color	Black

### Highlights

- Connects a SVGA port on a computer to a monitor with a DVI-I connector
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Supports Analog signals only
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Meets DVI DDWG Standard

### System Requirements

- Monitor or Projector with DVI-I connector, and PC with SVGA (HD15F) connector

### Package Includes

- DVI-A Male to HD15 Male, 6-ft. (1.83 m)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Cable Length (ft.)	6
Cable Length (m)	0.6
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.24
Shipping Weight (lbs.)	0.54
<b>CONNECTIONS</b>	
Side A - Connector 1	DVI-A (MALE)
Side B - Connector 1	HD15 (MALE)
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	RoHS-Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>