



Main

| | |
|------------------------------------|----------------------|
| Range | TeSys |
| Product or component type | Terminal block |
| Device short name | LAD |
| Accessory / separate part category | Connection accessory |
| Product compatibility | LRD15.. LR3D15.. |
| Quantity per set | Set of 1 |

Complementary

| | |
|-------------------------|----------------------|
| Connections - terminals | Screw terminals |
| Height | 3.23 in (82 mm) |
| Width | 1.77 in (45 mm) |
| Depth | 3.94 in (100 mm) |
| Net Weight | 0.22 lb(US) (0.1 kg) |

Ordering and shipping details

| | |
|-----------------------|---------------------------------|
| Category | 22341 - CONTACTOR,D,K,&F ACCESS |
| Discount Schedule | I12 |
| GTIN | 00785901599821 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 1 lb(US) (0.45 kg) |
| Returnability | No |
| Country of origin | FR |

Packing Units

| | |
|------------------------------|------------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 1.97 in (5 cm) |
| Package 1 width | 3.43 in (8.7 cm) |
| Package 1 Length | 4.13 in (10.5 cm) |
| Unit Type of Package 2 | S03 |
| Number of Units in Package 2 | 50 |
| Package 2 Weight | 7.84 lb(US) (3.558 kg) |
| Package 2 Height | 11.81 in (30 cm) |
| Package 2 width | 11.81 in (30 cm) |
| Package 2 Length | 15.75 in (40 cm) |
| Unit Type of Package 3 | P06 |
| Number of Units in Package 3 | 200 |
| Package 3 Weight | 45.64 lb(US) (20.7 kg) |
| Package 3 Height | 5.91 in (15 cm) |
| Package 3 width | 23.62 in (60 cm) |
| Package 3 Length | 31.50 in (80 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|