

GV7AC06

Combination kit between breaker and contactor, TeSys GV5 / GV7, for contactor LC1F115-185



Main

Range	TeSys
Product or component type	Kit for combination with connector type
Device short name	GV7AC
Range compatibility	TeSys GV5 motor circuit breaker TeSys GV7 motor circuit breaker TeSys F contactor
Accessory / separate part category	Connection accessory
Product compatibility	LC1F115...LC1F185

Complementary

Kit composition	Short terminal shield Adjustable mounting bracket(s) Terminal screw type connector
Quantity per set	Set of 1
Net Weight	1.21 lb(US) (0.55 kg)

Ordering and shipping details

Category	22366 - MAN STR PROTECTORS-GV1/GV3
Discount Schedule	I11
GTIN	00785901567301
Nbr. of units in pkg.	1
Package weight(Lbs)	2.48 lb(US) (1.12 kg)
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.62 in (9.2 cm)
Package 1 width	3.94 in (10 cm)
Package 1 Length	7.36 in (18.7 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	4
Package 2 Weight	10.57 lb(US) (4.794 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)


Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty


Warranty	18 months
----------	-----------

Combination of GV7R and TeSys Contactor LC1 F with Kit GV7AC0.



	a	b	c
GV7R + LC1F115 or F150 + GV7AC06	119	334	181
GV7R + LC1F185 + GV7AC06	119	338	188
GV7R + LC1F225 + GV7AC07	131	358	188
GV7R + LC1F265 + GV7AC07	131	364	215

Combination of GV7R and TeSys Contactor LC1F with Kit GV7 AC0.



	E	G	H
GV7R + LC1F115 + GV7AC06	44	85	120
GV7R + LC1F150 + GV7AC06	46	85	120
GV7R + LC1F185 + GV7AC06	48	85	120
GV7R + LC1F225 + GV7AC07	57	85	120
GV7R + LC1F265 + GV7AC07	60	85	120