



POWERING YOUR *life.*

# Model 201223

UPC 817198026312

Warranty 3 Years

## 5000

**STARTING WATTS**

Propane: 4500  
Natural Gas: 4050

## 4000

**RUNNING WATTS**

Propane: 3600  
Natural Gas: 3240

**RUN TIME** 14 hrs. **RUN TIME** 10.5 hrs. **NOISE LEVEL** 68 dBA



### NATURAL GAS READY!

INCLUDES 25 ft. natural gas hose kit.



### INTELLI GAUGE

4-MODE digital meter



### ELECTRIC START

Push-button start includes **BATTERY**



### COVERED OUTLETS

PROTECT outlets from the elements

Receptacles



**30 AMP**  
120V, L5-30R



**30 AMP RV**  
120V, TT-30R



**20 AMP**  
120V, 5-20R

### Specifications

<b>START TYPE</b>	Electric, Recoil
<b>VOLTAGE (V)</b>	120
<b>VOLTMETER</b>	Intelligauge
<b>ENGINE SIZE (cc)</b>	224
<b>FUEL TYPE</b>	Gasoline, Propane or Natural Gas
<b>GASOLINE CAPACITY (gal.)</b>	5
<b>OIL TYPE</b>	5W-30
<b>OIL CAPACITY (fl. oz.)</b>	20.3
<b>LOW OIL SHUT-OFF</b>	Yes
<b>EMISSIONS</b>	EPA III




## SHIELD®

**CARBON MONOXIDE  
AUTO-SHUTOFF SYSTEM**



OIL INCLUDED



Champion's 4000-watt natural gas ready generator features CO Shield® carbon monoxide auto shutoff system. Also operating on Tri-Fuel technology, allowing it to run on natural gas, gasoline, or propane. This unit meets ANSI/PGMA G300-2018 requirements and includes a 25-foot natural gas hose kit.

### Inside the box

<b>GENERATOR</b>	<b>PROPANE HOSE</b>
<b>WHEEL KIT</b>	<b>NATURAL GAS HOSE</b>
<b>BATTERY</b>	<b>OIL FUNNEL</b>
<b>ENGINE OIL</b>	<b>OPERATOR'S MANUAL</b>

### What You Need

**GASOLINE, PROPANE OR NATURAL GAS  
WRENCH OR SOCKET SET (METRIC)  
PLIERS**

\*Specifications, descriptions and illustrations are subject to change without notice.

**PACKAGE (gross)**  
Weight: 144 lb.  
Size: 29.1 × 20.5 × 20.9 in.

**PRODUCT (net)**  
Weight: 128 lb.  
Size: 29.1 × 20.5 × 20.9 in.

**CHAMPION POWER EQUIPMENT, INC.**  
12039 Smith Ave., Santa Fe Springs, CA 90670, USA  
www.championpowerequipment.com