

H₂Option[®] and H₂Optimum[™]

MaP PREMIUM Listed Ultra-High Efficiency Toilets



H₂Option

NEW
LOWER FLUSH
RATIO



H₂Optimum

NEW



*American
Standard*

H₂Option[®] and H₂Optimum[™]

MaP PREMIUM Listed Ultra-High Efficiency Toilets



Highest water efficient, gravity flush toilets available – Maximum water savings!


- Ultra-High Efficiency Toilets (UHETs) meet EPA WaterSense and MaP PREMIUM criteria*
- Choose either dual flush 0.92/1.28 gpf H₂Option or single flush 1.1 gpf H₂Optimum tank
- Siphon jet bowl technology with PowerWash[®] rim provides optimal UHET performance
- 12" rough-in configurations with fully glazed 2" trapways and a five year warranty
- EverClean[®] surface included at no extra cost



H₂Option Dual Flush
2886.218.020



H₂Optimum Single Flush
288AA.114.020



UHET PLATFORM	BOWL HEIGHT	BOWL TYPE	TANK TYPE	COLOR	UHET COMBINATION LESS SEAT	BOWL	TANK	
H ₂ Option Dual Flush	16-1/2"	Elongated	Unlined	020	2886.218.020	3705.216.020	4133A.218.020	
				021	2886.218.021	3705.216.021	4133A.218.021	
				222	2886.218.222	3705.216.222	4133A.218.222	
			Lined	020	2886.518.020	3705.216.020	4133A.518.020	
				021	2886.518.021	3705.216.021	4133A.518.021	
				222	2886.518.222	3705.216.222	4133A.518.222	
	15"	Elongated	Unlined	020	2887.218.020	3706.216.020	4133A.218.020	
				021	2887.218.021	3706.216.021	4133A.218.021	
				222	2887.218.222	3706.216.222	4133A.218.222	
			Lined	020	2887.518.020	3706.216.020	4133A.518.020	
				021	2887.518.021	3706.216.021	4133A.518.021	
				222	2887.518.222	3706.216.222	4133A.518.222	
		Round Front	Unlined	020	2889.218.020	3708.216.020	4133A.218.020	
				021	2889.218.021	3708.216.021	4133A.218.021	
				222	2889.218.222	3708.216.222	4133A.218.222	
			Lined	020	2889.518.020	3708.216.020	4133A.518.020	
				021	2889.518.021	3708.216.021	4133A.518.021	
				222	2889.518.222	3708.216.222	4133A.518.222	
	H ₂ Optimum Single Flush	16-1/2"	Elongated	Unlined	020	288AA.114.020	3705.216.020	4133A.114.020
		15"	Elongated			288CA.114.020	3706.216.020	
			Round Front			288DA.114.020	3708.216.020	

288AA.114.020 ONLY – MEETS THE AMERICANS WITH DISABILITIES ACT GUIDELINES AND ANSI A117.1 REQUIREMENTS FOR ACCESSIBLE AND USABLE BUILDING FACILITIES-CHECK LOCAL CODES

*MaP PREMIUM testing performed by IAPMO R&T Lab. MaP report conducted by Veritec Consulting Inc. and Koeller and Company.