


VX5VPS3001

Altivar Process ATV600, Altivar Process ATV900, Machine ATV340, wear part, fan for variable speed drives IP21, size 3

GENERIC IMAGE FOR



Main

Range of product	Altivar Process ATV600 Altivar Process ATV900
Accessory / separate part type	Fan kit
Accessory / separate part category	Cooling accessory

Complementary

Kit composition	Mounting bracket Instruction sheet Fan
Product compatibility	Variable speed drive ATV630 wall mount 7.5 kW 200...240 V Variable speed drive ATV630 wall mount 11 kW 200...240 V Variable speed drive ATV630 wall mount 15 kW 380...480 V Variable speed drive ATV630 wall mount 18 kW 380...480 V Variable speed drive ATV630 wall mount 22 kW 380...480 V Variable speed drive ATV930 wall mount 7.5 kW 200...240 V Variable speed drive ATV930 wall mount 11 kW 200...240 V Variable speed drive ATV930 wall mount 15 kW 380...480 V Variable speed drive ATV930 wall mount 18 kW 380...480 V Variable speed drive ATV930 wall mount 22 kW 380...480 V

Ordering and shipping details

Category	22205 - ATV630 FRAMES 1 & 2
Discount Schedule	CP4E
GTIN	00785901559054
Nbr. of units in pkg.	1
Package weight(Lbs)	1.39 lb(US) (0.63 kg)
Returnability	Yes
Country of origin	CN

Packing Units

Package 1 Height	0.750 dm
Package 1 width	1.720 dm
Package 1 Length	2.330 dm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------