



Scotch® Printable Flatback Paper Tape 256

Technical Data

May 2017

Product Description 3M™ Scotch® Printable Flatback Paper Tape 256 can be used for masking, bundling, holding and splicing operations needing colors for identification.

Product Construction	Backing	Adhesive	Color	Standard Roll Length
	Colored flatback paper	Rubber	Red, White, Green	60 yds. (55 m)

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

		ASTM Test Method
Adhesion to Steel:	35 oz./in. width (38 N/100 mm)	D-3330
Tensile Strength:	32 lbs./in. width (560 N/100 mm)	D-3759
Elongation at Break:	3.5%	D-3759
Total Thickness:	4.8 mils (0.12 mm)	D-3652
Temperature Use Range:	Up to 200°F (93°C) for one hour	

Features

- Adheres to a variety of paper, film, fabric and yarn surfaces.
- Printable with standard flexographic inks and is also easily marked with ballpoint pens, felt-tip pens, pencils and rubber stamps.
- Should not be subjected to outdoor exposure.

Application Ideas

- Can be used for a wide variety of bundling, banding, sealing, tabbing, defect flagging and holding applications where color for identification or coding is desired.
- Light to medium bundling applications.
- Banding items where color coding is required.
- Last lap end roll tabbing of paper, film, fabric, and yarns.

3M™ Scotch® Printable Flatback Paper Tape 256

Storage	Store under normal conditions of 60° to 80°F (16° to 27°C) and 40-60% R.H. in the original carton.
---------	----------------------------------------------------------------------------------------------------

Shelf Life	To obtain best performance, use this product within 12 months from date of manufacture.
------------	-----------------------------------------------------------------------------------------

Technical Information	The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.
-----------------------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Product Selection and Use	Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.
---------------------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Warranty, Limited Remedy, and Disclaimer	Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.
------------------------------------------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Limitation of Liability	Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.
-------------------------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

ISO 9001

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.



Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (fax)
www.3M.com/industrial

Printed in U.S.A.
©3M E 70-0709-1004-0 (5/17)