


PIG® Designer Series Adhesive-Backed Grippy® Floor Mat

GRP36901 Indoor Use on Concrete, Vinyl, Linoleum, Tile and Laminate Flooring, 3' W x 50' L, 1 roll



Make a floor safety fashion statement with our stylish 87% recycled mat. The Grippy Designer Series delivers a soft, colorful, environmentally friendly mat when appearance and sustainability matter.

- Aesthetically pleasing mat is ideal for entrances, aisles, walkways and liquid hazard areas in Class A buildings, retail, hospitality, restaurants and architectural spaces.
- Made from 87% post-consumer recycled plastic to help meet your LEED and sustainability initiatives.
- Adhesive-backed floor mat stays exactly where you put it with no shifting, bunching up or flipping over that causes slips, trips and falls.
- Soft, pliable construction provides a cushioned walking surface and is easy to apply and remove.
- Designer color options let you match your floor safety solution to your décor.
- Cuts to any length to provide a high-traction surface and adequate walk-off coverage anywhere you need it.
- Quickly absorbs liquids while trapping dust and dirt to keep floors clean, dry and safe.
- Stays in place for up to 3 to 6 months in moderate to high-traffic areas.
- Hides trapped dirt and salt but releases particles for easy cleaning with broom, vacuum, mop, wet vac, carpet scrubber or floor scrubber.
- Sticks to most commercial floor surfaces including concrete, vinyl, linoleum, ceramic tile, quarry tile and laminate flooring.
- Eliminates the hassles of rubber-backed mats; weighs less, saves you up to 50% per year on rental contracts and has a lower environmental impact.
- ADA compliant for wheelchairs and walkers; carts and pallet jacks roll right over it.
- Tested and Certified by the National Floor Safety Institute (NFSI): high-traction surfaces such as PIG Grippy Floor Mat have been proven to reduce slip-and-fall claims by as much as 90%.

- Mats take on the properties of absorbed liquids
- always take proper precautions when handling saturated absorbents.
- See Resources & Downloads section for product use guidance



Item#	Description	Dimensions	Weight
GRP36901-DM		3' W x 50' L	
GRP36901-MC		3' W x 50' L	
GRP36901-OT		3' W x 50' L	
GRP36901-SLT		3' W x 50' L	

Metric Equivalent:

Item#	Description	Dimensions	Weight
GRP36901-DM		91cm W x 15.2m L	
GRP36901-MC		91cm W x 15.2m L	
GRP36901-OT		91cm W x 15.2m L	
GRP36901-SLT		91cm W x 15.2m L	

Specifications

Absorbency Range	1 - 9.9 gal.
Dimensions	3' W x 50' L
Mat Weight	Mediumweight
Recycled Content	87% Post-Consumer Recycled Polyester Fabric
Absorbency	Up to 4 gal. per roll
Absorbency per	Up to 4 gal. per roll
Brand	PIG
Category	Grippy® Designer Series
Flammability Specifications	Flame Resistant - Will melt and self-extinguish
Fluid Absorbed	Oils; Coolants; Solvents; Water; Universal
Incinerable	Yes
Industry	Commercial Facilities/Retail
Intended Use	Indoor Use on Concrete, Vinyl, Linoleum, Tile and Laminate Flooring
Special Feature	Recycled Material
Storage Temp Range	Store between 32°F and 120°F
Temperature Limit	Surface temps from 45°F to 120°F

Traffic	Heavy Foot Traffic; Carts & Equipment
UV Resistant	Yes
Sold as	1 roll
# per Pallet	28
Composition	Absorbent: Polyester Adhesive Backing: Proprietary Adhesive Material
UNSPSC	47131901
Pigalog® Page Number	<u>Page 217</u>

Metric Equivalent

Absorbency per	Up to 15.1 L per roll
Absorbency	Up to 15.1 L per roll
Dimensions	91cm W x 15.2m L

Technical Information

Certifications, Approvals and Ratings

ADA Compliant, ANSI B101.1- 2009

Technical Documents

[PIG Adhesive-Backed Mats](#)

[The Complete Slip, Trip & Fall Risk Zone Audit](#)

[New Pig Adhesive-Backed Mat Disclaimer and Warranty Info](#)

[Instructions for PIG Grippy Mat Cleaning & Care Guide](#)

[Instructions for PIG Grippy Mat Application, Cleaning and Care Guide](#)

[Technical Data Sheet for PIG® Adhesive-Backed Grippy Mat](#)

[White Paper- Getting a Grip on Slips, Trips and Falls](#)

[White Paper- The Walk Zone Safety Report](#)

[29 CFR 1910.22\(a\)\(2\)](#)



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com