


HSM® SECURIO

B26 document shredder

Ideal for small working groups



- Ideal for up to 6 users
- Integrated light barriers start shredder automatically and switch it off after paper feed ends
- Anti-Jam Technology prevents jams when machine is overloaded
- Continuous Duty operation ensures continual shredding with no down time
- High user safety guaranteed by the folding safety elements which prevents unintentional intake
- Energy Management Control System EcoSmart: particularly low power consumption of 0.1 watt in standby mode
- Comprehensive safety system – UL Approved, CE – Certified
- Quiet operation while shredding
- Cutting Cylinder made from 100% solid steel for high cutting capacities
- Multifunction button with reversing function
- Inspection window to monitor filling level
- Casters for mobility
- Optional: Automatic oiler for cross cut and micro cut ensures long-time cutting performance and quality
- 34 gallon waste bag capacity; Part #HSM1815



HSM part#	HSM1800	HSM1801	HSM1803	HSM1802
Cutting type	Strip cut	Strip cut	Cross cut	Micro cut
Cutting size	1/8"	1/4"	3/16" x 1 1/8"	1/16" x 9/16"
Security level DIN 32757-1	2	2	3	4
Security level DIN 66399	P-2 / O-2 / T-2 / E-2	P-2 / O-2 / T-2 / E-2	P-4 / O-3 / T-4 / E-3 / F-1	P-5 / T-5 / E-4 / F-2
Cutting capacity per run in sheets	22 - 24	28 - 30	17 - 19	11 - 13
Cutting speed	13 ft / min	13 ft / min	13 ft / min	13 ft / min
Throat opening	11"	11"	11"	11"
Motor at max. no. of sheets	500W	500W	580W	580W
Motor power (horsepower)	0.67	0.67	0.78	0.78
Voltage	115 V / 60 Hz	115 V / 60 Hz	115 V / 60 Hz	115 V / 60 Hz
Dimensions (H x W x D)	26.6"x19.6"x15.6"	26.6"x19.6"x15.6"	26.6"x19.6"x15.6"	26.6"x19.6"x15.6"
Weight	53.4 lbs	53.4 lbs	58.2 lbs	58.2 lbs
Shred-bin volume	14.5 gallons	14.5 gallons	14.5 gallons	14.5 gallons
Cutting capabilities				

All technical specifications are approximate values. Technical and design modifications reserved.

HSM of America, LLC
419 Boot Road
Downingtown, PA 19335
www.hsmofamerica.com
Customer Service: 800.613.2110

Great Products, Great People.

HSM®