

**AXIS**  
WITH DYNEEMA® DIAMOND TECHNOLOGY **D2**



**HAND PROTECTION**

**RWGD110 CUT PROTECTION LEVEL A4 WORK GLOVE**



**RADIANS®**

**HEADQUARTERS**  
5305 Distriplex Farms Drive  
Memphis, TN 38141  
Toll Free: 877-723-4267  
Phone: 901-388-7776 • Fax: 901-266-2558  
[www.radians.com](http://www.radians.com)

[www.radians.com](http://www.radians.com)



## RWGD110 CUT PROTECTION WORK GLOVE



EN388:2003



4 5 4 4

1534g



Meets ANSI/ISEA 105:2016 Cut Level A4

### Tested to EN388:2003 Standards

for Abrasion Resistance, Blade Cut, Tear, and Puncture (4544)

RWGD110 TECHNICAL DATA	
LOAD WEIGHT	1534g
MATERIAL	13 Ga Salt-N-Pepper Dyneema Diamond (725 Dtex Yarn)
PALM	Black Micro Nitrile
COLOR	Salt-N-Pepper / Black
CUFF STYLE	Seamless Comfort Cuff
SIZES	S / M / L / XL / XXL
PACKAGING	6 poly bags of 12 individually polybagged pairs
CASE	72 pairs / 6 dozen
HANGTAG	No
COO	China

APPLICATIONS	
Construction	Automotive
Material Handling	Maintenance
Metal Fabrication	Oil & Gas

RWGD110				
PART NO.	SIZE	HEM COLOR	DOZEN UPC	MASTER PACK UPC
RWGD110S	Small	Green	10674326302109	20674326302106
RWGD110M	Medium	Brown/Coffee	10674326302116	20674326302113
RWGD110L	Large	Yellow	10674326302123	20674326302120
RWGD110XL	X-Large	Gray	10674326302130	20674326302137
RWGD110XXL	2X-Large	Navy Blue	10674326302147	20674326302144

RWGD110-SSH\_REV00\_4-14-17

Enhanced Dirt Masking Properties

Steel & Fiberglass Free

13 Ga Salt-N-Pepper Dyneema Diamond (725 Dtex Yarn)

TPR Overlays

Reinforced Thumb Crotch

Black Micro Nitrile

Radiates Heat Away To Help Keep You Cool

Durable & Washable For Long Lasting Protection

Excellent Abrasion Resistance



U.S. Pat. No. 9,241,519



### HEADQUARTERS

5305 Distriplex Farms Drive | Memphis, TN 38141  
 Toll Free: 877-723-4267 | Phone: 901-388-7776  
 Fax: 901-266-2558 | Web: www.radians.com