

**SGS**<sup>®</sup>  
Solid Carbide Tools

**VALUE AT THE SPINDLE<sup>®</sup>**

**A LITTLE  
SIMPLICITY  
GOES A LONG WAY!**



**SERIES 1**

- **4 FLUTE GENERAL PURPOSE END MILL**
- **VARIABLE INDEX**
- **30° HELIX ANGLE**
- **AVAILABLE IN SQUARE, BALL, & CORNER RADIUS END CONFIGURATIONS**
- **AVAILABLE IN FRACTIONAL & METRIC**
- **AVAILABLE UNCOATED, TI-NAMITE<sup>®</sup>, TI-NAMITE<sup>®</sup>-C, & TI-NAMITE<sup>®</sup>-A**



**SCAN THE CODE TO THE LEFT TO  
FIND YOUR SOLUTION  
TODAY!**

 **KYOCERA**



SERIES 1

### SQUARE END ITEMS

EDP	Series	LIST PRICE	NET PRICE	Cutting Diameter	Shank Diameter	Overall Length	Length of Cut	Shank Length	Corner Radius	Coating
39015	01S	\$20.67	\$8.82	0.1250	0.1250	1.5	0.5	1.0	•	TI-NAMITE®-C
39023	01S	\$28.69	\$12.24	0.1875	0.1875	2.0	0.6	1.4	•	TI-NAMITE®-C
91280	01S	\$204.28	\$87.15	0.2500	0.2500	2.5	0.8	1.8	•	DI-NAMITE
39139	01S	\$48.99	\$20.90	0.3125	0.3125	2.5	0.8	1.7	•	TI-NAMITE®
30179	01S	\$58.55	\$24.98	0.3750	0.3750	2.5	1.0	1.5	•	UNCOATED
30155	01S	\$69.89	\$29.82	0.4375	0.4375	2.8	1.0	1.8	•	UNCOATED
39163	01S	\$98.91	\$42.20	0.5000	0.5000	3.0	1.0	2.0	•	TI-NAMITE®
30381	01S	\$184.12	\$78.55	0.6250	0.6250	3.5	1.3	2.3	•	TI-NAMITE®-A
30026	01S	\$271.22	\$115.70	0.7500	0.7500	4.0	1.5	2.5	•	TI-NAMITE®-A
30173	01S	\$372.94	\$159.10	0.8750	0.8750	4.0	1.5	2.5	•	UNCOATED
30175	01S	\$398.57	\$170.03	1.0000	1.0000	4.0	1.5	2.5	•	UNCOATED

### CORNER RADIUS ITEMS

EDP	Series	LIST PRICE	NET PRICE	Cutting Diameter	Shank Diameter	Overall Length	Length of Cut	Shank Length	Corner Radius	Coating
38004	01C	\$26.09	\$11.13	0.1250	0.1250	1.5	0.5	1.0	•	TI-NAMITE®
38011	01C	\$31.02	\$13.23	0.1875	0.1875	2.0	0.6	1.4	•	UNCOATED
38020	01C	\$42.60	\$18.17	0.2500	0.2500	2.5	0.8	1.8	•	TI-NAMITE®
38033	01C	\$50.50	\$21.54	0.3125	0.3125	2.5	0.8	1.7	•	UNCOATED
38048	01C	\$68.57	\$29.25	0.3750	0.3750	2.5	1.0	1.5	•	TI-NAMITE®
38062	01C	\$121.36	\$51.77	0.5000	0.5000	3.0	1.0	2.0	•	TI-NAMITE®
38077	01C	\$192.55	\$82.14	0.6250	0.6250	3.5	1.3	2.3	•	UNCOATED
38088	01C	\$303.65	\$129.54	0.7500	0.7500	4.0	1.5	2.5	•	TI-NAMITE®
38102	01C	\$531.40	\$226.70	1.0000	1.0000	4.0	1.5	2.5	•	TI-NAMITE®

### BALL END ITEMS

EDP	Series	LIST PRICE	NET PRICE	Cutting Diameter	Shank Diameter	Overall Length	Length of Cut	Shank Length	Corner Radius	Coating
30116	01B	\$22.90	\$9.77	0.1250	0.1250	1.5	0.5	1.0	•	UNCOATED
39124	01B	\$34.08	\$14.54	0.1875	0.1875	2.0	0.6	1.4	•	TI-NAMITE®
91281	01B	\$217.44	\$92.76	0.2500	0.2500	2.5	0.8	1.8	•	DI-NAMITE
39140	01B	\$57.83	\$24.67	0.3125	0.3125	2.5	0.8	1.7	•	TI-NAMITE®
30184	01B	\$61.83	\$26.38	0.3750	0.3750	2.5	1.0	1.5	•	UNCOATED
30058	01B	\$88.88	\$37.92	0.4375	0.4375	2.8	1.0	1.8	•	TI-NAMITE®-A
30062	01B	\$124.27	\$53.01	0.5000	0.5000	3.0	1.0	2.0	•	TI-NAMITE®-A
30386	01B	\$208.87	\$89.10	0.6250	0.6250	3.5	1.3	2.3	•	TI-NAMITE®-A
30187	01B	\$287.11	\$122.48	0.7500	0.7500	4.0	1.5	2.5	•	UNCOATED
39174	01B	\$491.03	\$209.47	0.8750	0.8750	4.0	1.5	2.5	•	TI-NAMITE®
30188	01B	\$506.58	\$216.11	1.0000	1.0000	4.0	1.5	2.5	•	UNCOATED



SCAN THE CODE OR VISIT

<https://www.kyocera-sgstool.com/digital-catalog>

TO LEARN MORE!