

PS/2 to USB Converter

MODEL NUMBER: 0DT60002



Description

Preserve Your IT investments

Flexible USB Support

- Supports USB keyboard with USB mouse
- Supports USB keyboard with PS/2 mouse
- Supports USB mouse with PS/2 keyboard

Features

- Compatible with PS/2 servers / KVM switches / KVM extenders
- Pure hardware solution - no software/network conflicts
- No need for external power
- Compact size
- Plug & play
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

Highlights

- Compatible with PS/2 servers/KVM switches/KVM extenders
- Pure hardware solution - no software/network conflicts
- No need for external power
- Compact size
- Plug & play
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- PS/2 Computer / KVM Switch / KVM Extender
- USB and/or PS/2 keyboard and mouse
- Compatible with most keyboards; supports 104 keys only

Package Includes

- PS/2 to USB Converter



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	654518212235
Technology	PS/2; USB
INPUT	
Product Length (in.)	11.4
PHYSICAL	
Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.5mm
Material of Construction	ABS
Shipping Dimensions (hwd / cm)	13.97 x 9.91 x 1.27
Shipping Dimensions (hwd / in.)	5.50 x 3.90 x 0.50
Shipping Weight (kg)	0.08
Shipping Weight (lbs.)	0.18
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	41 to 104 F (5 to 40 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Relative Humidity	0% to 80% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	(2) MINI DIN-6 (MALE)
Side B - Connector 1	(2) USB A (FEMALE)
Connector Plating	Nickel
Contact Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 1.1 (up to 12 Mbps)
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>