

## BRADY B-853 CARDSTOCK TAG

TDS No. B-853  
Effective Date: 11/17/2003

### **Description:**

Brady B-853 is a surface printed cardstock tag.

### **Details:**



### **Use:**

Brady B-853 is used for temporary tagging in a non harsh environment.

### **Substrate Type:**

Paper cardstock

### **Standard Material Colors:**

White, yellow, red, green, fluorescent orange, fluorescent red, fluorescent green, chartreuse and orange

### **Standard Legend Colors:**

Black, red, green, magenta, orange, yellow, and blue

### **Thickness (ASTM D 1593):**

Total: 0.010 in. (0.25mm)

### **Service Temperature:**

-40°F to 194°F (-40°C to 90°C)

### **Average Outdoor Durability:**

Not recommended for outdoor use.

### **Chemical Resistance:**

Not recommended for chemical exposure.

### **Shelf Life:**

Indefinite when stored at 70°F (21°C) and 40% to 50% R.H.

### **Trademarks:**

Signmark® is a registered trademark of Brady Worldwide, Inc.  
ASTM: American Society for Testing and Materials (U.S.A.)  
All S.I. Units (metric) are mathematically derived from the U.S. Conventional Units.

**Note:** All values shown are averages and should not be used for specification purposes.

Test data and test results contained in this document are for general information only and shall not be relied upon by Brady customers for designs and specifications, or be relied on as meeting specified performance criteria. Customers desiring to develop specifications or performance criteria for specific product applications should contact Brady for further information.

Product compliance information is based upon information provided by suppliers of the raw materials used by Brady to

manufacture this product or based on results of testing using recognized analytical methods performed by a third party, independent laboratory. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

## **WARRANTY**

Brady products are sold with the understanding that the buyers will test them in actual use and determine for themselves their adaptability to their intended uses. Brady warrants to the buyers that its products are free from defects in material and workmanship, but limits its obligation under this warranty to replacement of the product shown to Brady's satisfaction to have been defective at the time Brady sold it. This warranty does not extend to any persons obtaining the product from the buyers. This warranty is in lieu of any other warranty, express or implied, including, but not limited to, any implied warranty of merchantability or fitness for a particular purpose, and of any other obligations or liability on Brady's part. Under no circumstances will Brady be liable for any loss, damage, expense, or consequential damages of any kind arising in connection with the use, or inability to use, Brady's products.

Copyright 2016 Brady Worldwide, Inc. | All Rights Reserved  
Material may not be reproduced or distributed in any form without written permission.

---

Brady North America | 6555 W. Good Hope Rd | Milwaukee, WI 53223 | USA | Tel: 414-358-6600 | Fax: 800-292-2289