



 **CRESCENT**<sup>®</sup>

**Pipe Wrenches**

**Trusted by the Trades.**




## More Power At Every Turn

These new Crescent Pipe Wrenches have been redesigned from the ground up to be lighter, quicker to adjust, and more comfortable to use. But even more, they've been designed to deliver the most powerful pipe grip ever with our new straight wrenches offering larger bite surfaces and exclusive K9™ 30-degree angle access jaws that give you massive turning power, even in the tightest, most restricted situations.

### 2X Faster Adjustment Speed

Adjustment ring thread pitch angled for faster opening and closing of wrench jaw



### Best Access

K9™ Jaw Technology allows teeth to bite in an arc of 30 degrees – much greater than typical pipe wrench operation limits – for greater access in tight spaces

### 40% Less Weight

To help reduce user fatigue, weight has been cut in low stress areas of aluminum wrenches, making them up to 40% lighter than cast iron wrenches. Our cast iron wrenches have also been design optimized to be up to 10% lighter than competitive wrenches.

### Best Grip

Handle shape optimized for maximum power and user comfort

Straight Pipe Wrenches come in both cast aluminum and cast iron. Aluminum models are up to 40% lighter than typical cast iron wrenches with thicker cross-sections in high-stress areas for exceptional strength. Our cast iron wrenches have also been optimized for strength, weighing up to 10% less than competitive products.

Our Self-Adjusting Pipe Wrenches offer compact size, light weight, and a jaw design that locks open for easier placement onto pipes in tight spots.

### Ease of Use

The jaw locks in the fully open position, allowing users to easily position and remove the wrench from the work piece



### One-Handed Use

Ratcheting adjustable head allows for one-handed use with a greater range of pipe and fastener sizes.



### Best Grip

Handle has been optimized to user grip

### Best Access

Extended lower jaw increases access and allows for quick pipe grip in confined spaces




Patent Pending

30° ANGLE ACCESS



\*Aluminum models



## A Wrench For Every Job

No matter what the challenge, Crescent has the pipe wrench you need to get jobs done fast and professionally. Whether you prefer straight or self-adjusting, aluminum or traditional cast iron, we offer the styles and sizes that will work the best – with the added benefit of our new K9™ Jaw Technology that allows our straight wrenches to work in an arc of 30 degrees, giving you unprecedented access. For the best grip, choose Crescent.



CIPW10



CIPW14



CIPW18



CAPW10



CAPW14



CAPW14L



CAPW18



CAPW24



CPW12



CPW12S



CPW16S

Item No	Description	Shelf Pack Quantity	UPC	Shelf Pack Code	Product Package Dimensions	Product Weight
CIPW10	Cast Iron, 10in SLIM JAW	4	37103336491	10037103336498	9.8"L x 2.75"W x 1.15"H	1.74 lbs.
CIPW14	Cast Iron 14in GRIP-30	3	37103336507	10037103336504	12.9"L x 1.38"W x 3.15"H	3.51 lbs.
CIPW18	Cast Iron, 18in GRIP-30	3	37103336514	10037103336511	15.87"L x 3.74"W x 1.57"H	5.69 lbs.
CAPW14	Aluminum, 14in GRIP-30	3	37103332325	10037103332322	18.74"L x 5.0"W x 1.74"H	2.14 lbs.
CAPW18	Aluminum, 18in GRIP 30	3	37103332332	10037103332339	15.87"L x 3.64"W x 1.57"H	3.37 lbs.
CAPW24	Aluminum, 24in	2	37103332349	10037103332346	21.46"L x 4.49"W x 1.85"H	4.99 lbs.
CAPW10	Aluminum, 10in SLIM JAW	4	37103336521	10037103336528	12.21"L x 2.75"W x 1.15"H	0.98 lbs.
CAPW14L	Aluminum, 14in, Long Handle GRIP-30	3	37103336538	10037103336535	18.04"L x 1.38"W x 3.15"H	2.63 lbs.
CPW12	Self Adjustable, 12in, Grip	2	37103282781	10037103282788	15.3"L x 3.4"W x 1.0"H	1.3 lbs.
CPW12S	Self Adjustable, 12in, Steel Handle	2	37103332301	10037103332308	15.15"L x 3.4"W x 1.0"H	1.3 lbs.
CPW16S	Self Adjustable, 16in, Steel Handle	3	37103332318	10037103332315	16.52"L x 3.74"W x 1.23"H	3.1 lbs.