



## Model AN613 Parts List

A = Standard Equipment

O = Circuit Diagram

Item#	Part#	Description	Q'ty	Unit
1	HY00000655	HEX.SOCKETC.S.HEADSCREWM6X20	1	PC.
2	HY00000632	SLEEVE6	1	PC.
3	HY00000596	EXHAUSTCOVER	1	PC.
4	HY00000627	RUBBERRING10	1	PC.
5	HY00000156	HEX.SOCKET HEAD BOLT M5X25	4	PC.
6	HY00000162	SPRING WASHER 5	4	PC.
7	HY00000160	FLAT WASHER 5	4	PC.
8	HY00001064	TOP CAP COMPLETE	1	
9	HY00001065	TOPCAP GASCKET	1	
10	HY00001101	COMPRESSION SPRING 45	1	
11	HY00000455	HEADVALVEGUIDE	1	PC.
12	HY00000677	HEX.SOCKETBUTTONHEADSCREWM6X12	1	PC.
13	HY00000409	ORING30.5	1	PC.
14	HY00001102	HEAD VALVE	1	
15	HY00000141	O-RING 45	1	PC.
16	HY00000020	O-RING 36	1	PC.
17	HY00000517	REARCUSHION	1	PC.
18	HY00001066	VALVE SHEET GUIDE	1	
19	HY00000452	VALVESHEET	1	PC.
20	HY00001067	CYLINDER	1	
21	HY00000405	ORING47	1	PC.
22	HY00000402	ORING44	1	PC.
23	HY00000785	CYLINDER SEPARATER	1	PC.
24	HY00000143	O-RING 67	1	PC.
25	HY00000139	O-RING 35	1	PC.
26	HY00001068	DRIVER COMPLETE	1	
27	HY00001087	FRONT CUSHION	1	
28	HY00001069	HOUSINGCOMPLETE	1	
C10	HY00000828	CAUTION LABEL	1	PC.
29	HY00000790	COMPRESSION SPRING 6	1	PC.
30	HY00001070	CONTACT ARM ASSEMBLY	1	
D10		INC. 31-39		
31	HY00000791	UPPER YOKE	1	PC.
32	HY00000526	STEELBALL3	1	PC.
33	HY00000470	COMPRESSIONSPRING2	1	PC.
34	HY00000792	ADJUSTER DIAL	1	PC.
35	HY00000793	ADJUSTER SHAFT	1	PC.
36	HY00000114	SPRING PIN 2.5-16	1	PC.
37	HY00000397	ORING5	1	PC.
38	HY00000795	RING SPRING 5	1	PC.
39	HY00001071	CONTACT ARM	1	
40	HY00000165	SPRING PIN 3-28	2	PC.
41	HY00000805	TRIGGER BASE	1	PC.
42	HY00000165	SPRING PIN 3-28	2	PC.
43	HY00000135	O-RING 15	1	PC.
44	HY00000137	O-RING 17	1	PC.
45	HY00000806	O-RING 7	1	PC.
46	HY00000132	O-RING 7	1	PC.
47	HY00000807	O-RING 10	1	PC.

48	HY00000808	TRIGGER VALVE GUIDE	1 PC.
49	HY00000809	PILOT VALVE	1 PC.
50	HY00000810	COMPRESSION SPRING 2	1 PC.
51	HY00000812	O-RING 4	1 PC.
52	HY00000814	TRIGGER VALVE CASE	1 PC.
53	HY00000705	COMPRESSION SPRING 10	1 PC.
54	HY00000811	TRIGGER VALVE STEM	1 PC.
55	HY00000813	O-RING 3	2 PC.
56	HY00000659	STOP RING E-3	1 PC.
57	HY00000520	SLEEVE4	1 PC.
58	HY00000526	STEELBALL3	1 PC.
59	HY00000590	COMPRESSIONSPRING2	1 PC.
60	HY00000518	LEVER4	1 PC.
61	HY00000815	TRIGGER COMPLETE	1 PC.
	D10	INC. 62-64	
62	HY00000436	TRIGGER	1 PC.
63	HY00000816	IDLER	1 PC.
64	HY00000114	SPRING PIN 2.5-16	1 PC.
65	HY00001073	DRIVER GUIDE ASSEMBLY	1
	D10	INC. 66-77	
66	HY00000164	RETAINING RING R-24	1 PC.
67	HY00000187	CUP WASHER 5	1 PC.
68	HY00000207	RUBBER RING 16	1 PC.
69	HY00000148	COMPRESSION SPRING 6	1 PC.
70	HY00001074	FEEDING CLAW	1
71	HY00000206	URETHAN RING 3	1 PC.
72	HY00000150	COMPRESSION SPRING 7	1 PC.
73	HY00000136	O-RING 17	1 PC.
74	HY00000168	PIN 4	1 PC.
75	HY00000129	O-RING 8	1 PC.
76	HY00001075	PISTON	1
77	HY00001076	DRIVER GUIDE COMPLETE	1
78	HY00000820	O-RING 41	1 PC.
79	HY00000819	O-RING 4	1 PC.
80	HY00001044	HEX.SOCKET HEAD BOLT M6X20	4
81	HY00001077	PIN 4	1
82	HY00001078	LOCK LEVER	1
83	HY00001079	DOOR	1
84	HY00000206	URETHAN RING 3	1 PC.
85	HY00001080	PIN 4.5	1
86	HY00001081	NAIL HOLDER	1
87	HY00000548	COMPRESSIONSPRING4	1 PC.
88	HY00001082	CHECK CRAW	1
89	HY00000548	COMPRESSIONSPRING4	1 PC.
90	HY00000206	URETHAN RING 3	1 PC.
91	HY00001083	COMPRESSION SPRING 5	1
92	HY00001084	FLAT WASHER 3	1
93	HY00001042	SPRING WASHER 3	1
94	HY00001043	HEX.SOCKET HEAD BOLT M3X8	1
95	HY00001048	INLET CAP ASSEMBLY A	1
	D10	INC. 96-100,102-106	
96	HY00000573	DUSTERBUTTON	1 PC.
97	HY00000599	VALVEGUIDE	1 PC.
98	HY00000397	ORING5	1 PC.
99	HY00000513	VALVESTEM	1 PC.
100	HY00001049	INLET CAP A	1

101	HY00000580	SEALRING	1 PC.
102	HY00000046	PIN 2-10	1 PC.
103	HY00000589	COMPRESSIONSPRING5	1 PC.
104	HY00000399	ORING8.5	1 PC.
105	HY00000037	O-RING 3	2 PC.
106	HY00000054	SPRING PIN 2.5-18	1 PC.
107	HY00000155	HEX.SOCKET HEAD BOLT M5X12	1 PC.
108	HY00000162	SPRING WASHER 5	1 PC.
109	HY00000803	HOOK	1 PC.
110	311006-A	ONE TOUCH JOINT	1 PC.
111	HY00001050	HEX.SOCKETHEADBOLT M4X25	4
112	HY00000070	FLAT WASHER4	4 PC.
113	HY00000157	HEX.SOCKET HEAD BOLT M6X25	1 PC.
114	HY00000901	WASHER 6	1 PC.
115	HY00000858	HEX. LOCK NUT M6	1 PC.
116	HY00000206	URETHAN RING 3	1 PC.
117	HY00001052	MAGAZINE CAP	1
118	HY00000198	HOLDER CAP	1 PC.
119	HY00001053	CHANGE PLATE	1
120	HY00001054	MAGAZINE COMPLETE	1
121	HY00000208	RUBBER PLATE 6-19	1 PC.
122	HY00001056	TENSION SPRING 5	1
123	HY00000198	HOLDER CAP	1 PC.
124	HY00001051	MAGAZINE ASSEMBLY	1
	D10	INC. 118-123	
125	HY00001055	PIN 4	1
126	HY00001072	NOSE ADAPTER	1
127	HY00001063	HEX.SOCKET HEAD BOLT M6X18	1
128	HY00001062	FLAT WASHER 6	1
129	HY00001045	RUBBER PIN 5	1
130	HY00001046	COVER	1
132	HY00001061	SLEEVE 6	1
133	HY00001060	CONTACT ARM COVER	1
A01	HY00000951	SAGETY GOGGLE	1
A02	HY00001072	NOSE ADAPTER	1
A03	181434-7	OIL SUPPLY	1
A04	HY00001104	HEX. WRENCH 3	1
A05	HY00001105	HEX. WRENCH 4	1
A06	HY00000953	HEX. WRENCH 5	1