

Jumbo Swan Wax with Urethane



DESCRIPTION

Black Swan's Jumbo Swan Wax with Urethane is a 100% pure wax for setting all floor outlet toilet bowls. This ring contains 40% more wax than the regular **Swan Wax with Urethane**. Ideal to use where the regular ring does not provide enough wax to make a good seal. **Jumbo Swan Wax with Urethane** is a urethane gasket made of a tough, flexible and durable urethane foam. This urethane gasket is impregnated with wax. The combination of urethane foam and the wax makes the ring a stronger, more resistant ring than regular rings and is guaranteed for 10 years. Can be used for setting all floor outlet toilet bowls. The gasket forms a water tight, gas tight and odor tight seal. Will not support bacteria. Fits 3" and 4" waste lines. Meets Federal Specification TT-P-1536A.

DIRECTIONS

1. Be sure the wax ring is at room temperature (about 70° F). If wax ring is too cold a good seal may not be made or the toilet bowl could crack while making the installation.
 2. With the toilet bowl upside down on a protective pad or blanket, place the wax ring around the discharge opening. Press firmly to assure adhesion when the toilet is inverted.
 3. Using the **Black Swan's Stainless** or **Stay Soft Putty**, make a putty ring about 1 inch high around the outside rim of the toilet. This will make a seal between the toilet rim and the floor.
 4. Carefully set the toilet down on bolts and twist bowl slightly to spread wax and putty to make a tight seal. Tighten bolts carefully to prevent breaking the bowl.
-

ACCESSORIES

Black Swan also sells **Jumbo Swan Wax with Urethane** with closet bolts included in the package. Since closet bolts are necessary to make the installation, this is a nice package to offer the end user.

1. Stock number 04395 is **Jumbo Swan Wax with Urethane** with two 1/4" X 2-1/4" brass bolts, two brass plated nuts, two brass plated washers, and two plastic stand-up washers.
2. Stock number 04396 is **Jumbo Swan Wax with Urethane** with two 1/4" X 2-1/4" brass bolts, four brass plated nuts and four brass plated washers.
3. Stock number 04400 is **Jumbo Swan Wax with Urethane** with two 1/4" X 2-1/4" brass plated bolts, two brass plated nuts, two brass plated washers and two plastic stand-up washers.
4. Stock number 04401 is **Jumbo Swan Wax with Urethane** with two 1/4" X 2-1/4" brass plated bolts, four brass plated nuts and four brass plated washers.

GHS LABEL INFORMATION

PICTOGRAM: None

SIGNAL WORD: None

HAZARDOUS STATEMENT: None

PRECAUTIONARY STATEMENTS

FIRST AID:

Skin: First aid is not normally required. Wash affected area thoroughly with waterless cleaner and/or soap and water. If irritation persists, consult a physician.

Eyes: First aid is not normally required. Flush with large amounts of water for 15 minutes, holding eyelids open. Consult a physician if irritation persists.

Ingestion: First aid is not normally required. If swallowed, give two glasses of water to drink. Never give anything by mouth to an unconscious person. Do not induce vomiting. Consult a physician.

Inhalation: None

STORAGE:

Store away from flame, heat (110° F maximum to keep wax rings from melting or deforming in shape) and strong oxidizing agents. Do not stack cases more than seven high on each pallet. .

DISPOSAL:

Dispose of container in accordance with federal, state or local regulations.

UPC NUMBER AND CARTON INFORMATION

STOCK NO.	SIZE	UPC NUMBER	CARTON CUBIC FEET
04390	---	0 54647 04390 6	1.37
04395	---	0 54647 04395 1	1.37
04396	---	0 54647 04396 8	1.37
04400	---	0 54647 04400 2	1.37
04401	---	0 54647 04401 9	1.37