

# AL2500RK

## PowerPact R-FRAME MOULDED CASE CIRCUIT BREAKERS 2500A MECHANICAL LUG KIT



### Main

Range of product	Compact NS1600b...3200
Product or component type	Mechanical lug
Accessory / separate part category	Connection accessory
Quantity per set	Set of 2
Circuit breaker type	R-Frame

### Complementary

Product compatibility	PowerPact R PowerPact
Line Rated Current	2500 A
Material	Aluminium
Mounting mode	Unit mount
Location of connection	Downstream Upstream
AWG gauge	AWG 1/0...750 kcmil aluminium/copper
Kcmil size	750 kcmil
Tightening torque	60.18...64.61 Lbf.In (6.8...7.3 N.m) (AWG 1/0...750 kcmil) (AWG 1/0...350 kcmil)

### Environment

Product certifications	CSA UL
------------------------	-----------

### Ordering and shipping details

Category	01250 - M,P,R FRAME ACCESSORIES ONLY
Discount Schedule	DE2
GTIN	00785901441304
Nbr. of units in pkg.	1
Package weight(Lbs)	0.76 lb(US) (0.34 kg)
Returnability	Yes
Country of origin	US

### Packing Units

Package 1 Height	2.50 in (6.350 cm)
Package 1 width	5.00 in (12.700 cm)
Package 1 Length	6.50 in (16.510 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------