

Rolling Counter Shutters

M722



Made In U.S.A.

FINISH OPTIONS:

- Aluminum- Clear anodized
- Painted Steel- white topcoat
- Painted Steel- gray topcoat

40-year film integrity and a 35-year no-chalk/no-fade limited paint warranty.

STANDARD FEATURES:

- Flat slats -1-1/2" or 1-1/2" profile
- Steel end-locks- other options available
- Enclosed hood
- Slide bolt locks
- Face-of-wall mount
- Aluminum angle bottom bar with weather seal
- 2-Year limited warranty
- Manual or crank operation

M722 Series Rolling Counter Shutters are designed for commercial, government, medical or institutional applications and provide the security you need while delivering smooth, quiet, and effortless operation for years of dependable service.

These high quality shutters are available in both clear anodized aluminum or painted steel and offer a compact design requiring minimal headroom. They are the perfect choice for pharmacies, cafeterias, concession areas, ticket counters, nurse/hospital desks and numerous other countertop applications.



 **American**TM
garage door supply inc.

722 SERIES ROLLING SHUTTER

MODEL M722A (ALUMINUM) | MODEL M722(G OR W) PAINTED STEEL

Drum/Axle Assembly | Barrel fabricated from minimum 4-1/2" O.D. pipe, with 1" tension and drive shaft and provided with threaded rings or lugs welded to barrel for curtain assembly. Springs to be oil tempered grease packed helical torsion type.

Slats | 1-1/2" flat slat clear anodized aluminum or galvanized steel with super durable polyester paint in white or gray.

Bottom Bar | Extruded aluminum angle bottom bar standard for aluminum and steel doors. Both available with bottom weather seal.


Hood | Clear anodized aluminum hood is standard with aluminum curtain, 24-ga. steel included with steel curtains.

Operation | All standard door models doors include crank or manual operation



Guides | Extruded two piece aluminum guides are standard for all aluminum and steel doors.

Endlocks | Steel endlocks each end of alternate slats.

Locks | Dual slide bolt locks are standard.



SPECIFICATION DETAILS




EXTRUDED ALUMINUM GUIDE
FACE OF WALL DETAIL




Made In U.S.A.

Standard Features:

722 Series	Curtain	Color	Guides	Bottom Bar	Hood
Model M722W Model M722G	22-Ga. Steel 22-Ga. Steel	White Gray	Aluminum Aluminum	Aluminum Aluminum	24-Ga. Steel 24-Ga. Steel
Model M722A	.050 Aluminum	Clear Anodized	Aluminum	Aluminum	Aluminum



EXTRUDED ALUMINUM
FLAT SLAT



22 GAUGE STEEL
FLAT SLATS

Illustrations shown are for general reference and should be verified for construction purposes.