



Blacktop Crack Filler

Fill cracks in blacktop up to ¼" wide

©TCC Materials • March 2016 • Version 1.1

PRODUCT DESCRIPTION

SAKRETE® Blacktop Crack Filler is used to fill cracks up to ¼ in. (6 mm) wide in blacktop to help stop damaging water penetration. Ideal for repairs prior to driveway sealing.

WHEN/WHERE TO USE

- Any blacktop surface cracks, such as driveways

ADVANTAGES

- Seals cracks for longer wearing blacktop surfaces
- Helps stop damaging water penetration

PACKAGING

1 quart (0.95 L) bottle (BOM 120041)
1 gallon (3.785 L) bottle (BOM 120039)

TYPICAL YIELD

- One quart bottle will fill approximately 40 ft. (12.2 m) of crack at ¼ in. (6 mm) deep by ¼ in. (6 mm) wide.
- One gallon bottle will fill approximately 160 ft. (48.7 m) of crack at ¼ in. (6 mm) deep by ¼ in. (6 mm) wide.

SURFACE PREPARATION

Clean all dirt and loose materials from cracks. Deep cracks should be filled with clean fine sand or backer rod to within ¼ in. of the surface.

APPLICATION

Shake container well to ensure a uniform mix before application. Prior to use, place container in a warm location or submerge in hot water for better flowability. Pour material into the cracks, do not fill cracks that are deeper than ¼ in. (6 mm) in one application. If more than one layer is required, wait 5 days between applications.

NOTE: Proper application and installation of all SAKRETE products are the responsibility of the end user.

CURING

Full cure can take up to 5 days depending on weather conditions. Keep traffic off the area during this time. If it is necessary to open area to traffic before Blacktop Crack Filler is fully cured, sprinkling sand on the patch will help prevent tracking. If driveway sealer is to be applied, wait 5 days after applying crack filler before applying driveway sealer.

CLEAN UP

Warm, soapy water may be helpful for cleaning hands and tools while material is wet.

WARNING

Avoid contact with eyes, skin, and clothing. Wash thoroughly after handling. Exposure may result in irritation of the skin. **FIRST AID:** In case of eye contact, flush immediately with plenty of water for at least 15 minutes and get prompt medical attention; for skin, wash thoroughly with plenty of soap and water. If irritation persists, get medical attention. **KEEP OUT OF REACH OF CHILDREN.** READ and UNDERSTAND the Safety Data Sheet (SDS) before using this product.

LIMITED WARRANTY

The manufacturer warrants that this product shall be of merchantable quality when used or applied in accordance with the manufacturer's instructions. This product is not warranted as suitable for any purpose other than the general purpose for which it is intended. This warranty runs for one (1) year from the dates the product is purchased. **ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ON THIS PRODUCT IS LIMITED TO THE DURATION OF THIS WARRANTY.** Liability under this warranty is limited to

replacement of defective products or, at the manufacturer's option, refund of the purchase price **CONSEQUENTIAL AND INCIDENTAL DAMAGES ARE NOT RECOVERABLE UNDER THIS WARRANTY.**

SAKRETE® and the background design are registered trademarks of SAKRETE of North America LLC, Charlotte, NC 28273 • ©2006. SAKRETE® is manufactured under license from SAKRETE of North America LLC.

Helpful Items:



Shelf Life	One year in original, unopened container
Storage Conditions	Store dry at 40-100°F (4°C -37° C).
Color	Black

KEEP FROM FREEZING

WARNING: INJURIOUS TO EYES

KEEP OUT OF REACH OF CHILDREN