



RADIANS® HAND PROTECTION

RWG604 CUT PROTECTION LEVEL A4 WINTER WORK GLOVE



HEADQUARTERS
5305 Distriplex Farms Drive
Memphis, TN 38141
Toll Free: 877-723-4267
Phone: 901-388-7776 • Fax: 901-266-2558
www.radians.com

www.radians.com



RWG604

ANSI CUT LEVEL

4

RWG604 CUT PROTECTION LEVEL A4 WINTER WORK GLOVE



EN388:2003



4 5 4 4



Meets ANSI/ISEA 105:2016 Puncture Level 5



Meets ANSI/ISEA 105:2016 Abrasion Level 5

1785g



Meets ANSI/ISEA 105:2016 Cut Level A4

Tested to EN388:2003 Standards
for Abrasion Resistance, Blade Cut, Tear, and Puncture (4544)

RWGD604 TECHNICAL DATA

LOAD WEIGHT	1785g
MATERIAL	13 Gauge Blue and White HPPE Shell
PALM	Black Micro Nitrile
COLOR	Blue & White / Black / Hi-Viz Green
CUFF STYLE	Seamless Comfort Cuff
SIZES	S / M / L / XL / XXL
PACKAGING	6 poly bags of 12
CASE	72 pairs / 6 dozen
HANGTAG	No
COO	China
SOLD BY	Dozens

APPLICATIONS

Automotive	Material Handling
Bottling	Metal Fabrication
Cold Conditions	Mining
Construction	Petrochem Industry
General Assembly	Recycling
Glass Cutting	Sharp Parts
HVAC	Sheet Metal Handling
Manufacturing	Warehousing

RWG604

PART NO.	SIZE	HEM COLOR	PAIR UPC	DOZEN PACK UPC	MASTER PACK UPC
RWG604S	Small	Green	674326274759	10674326294756	20674326294753
RWG604M	Medium	Brown/Coffee	674326294742	10674326294749	20674326294746
RWG604L	Large	Yellow	674326285962	10674326285969	20674326285966
RWG604XL	X-Large	Gray	674326285979	10674326285976	20674326285973
RWG604XXL	2X-Large	Navy Blue	674326285986	10674326285983	20674326285980

2 Ply 13 Gauge Blue and White HPPE Outer Shell
High Performance Polyethylene for Cut Resistance



TPR Overlays
Provides Added Protection



Black Micro Nitrile Palm Coating
Provides Excellent Protection from Abrasion in Wet or Dry Applications

Seamless Cuff Design
Provides a Comfortable Fit

7 Gauge Acrylic Terry Liner
Provides Warmth in Cold Conditions

U.S. Pat. No. 9,241,519



HEADQUARTERS

5305 Distriplex Farms Drive | Memphis, TN 38141
P: 901-388-7776 | F: 901-266-2558
877-723-4267 | www.radians.com