

# XStream®

## Interior Mount Warning Light

### FEATURES

- Solaris® LED reflector technology for better optical efficiency and superior off-axis warning
- SpectraLux® multicolor LED technology in combinations of Amber, Blue, Green, Red, and White
- Incorporates FSLink® shared flash pattern set which provides the ability to synchronize with other FSLink products
- XStream models can be set to a steady burn pattern, and then programmed to synchronize with other FSJoin products
- FSJoin™ enables the synchronization of functions, operation, and flash patterns across multiple warning devices and multiple vehicles
- Each light head includes three colors with (6) LEDs of each color [(18) LEDs total]
- Low-profile design
- Available in single- or dual-head models
- Black polycarbonate housing
- Each model features two recessed buttons, one to change flash pattern and other for color mode
- (25) Flash patterns including random and steady; (10) color modes
- Versatile mounting brackets and three different length snap-on flash guards included
- Choice of accessory plug or wired models
- Accessory plug models include two switches for on/off and steady-burn
- Five-year warranty

### APPROVALS

- SAE J845 Class 1
- SAE J595 Class 1
- CCR Title 13

### FS TECHNOLOGIES



### Built-in Versatility

XStream® is an interior mount LED warning light that can be installed almost anywhere inside a police car, fire commander and volunteer fire vehicle, or work truck. XStream is available in single- or dual-head configurations and with accessory plug or wire leads that allow for synchronization. Ideal for dash/deck, headliner, and window mount applications, each model includes a light head, (2) suction cups, bail and pivot brackets, mounting hardware and three different length snap-on flash guards, making installation quick and versatile.

Every model is built with Federal Signal's Solaris® LED reflector for superior optical performance. In addition, SpectraLux® multicolor LED technology provides the ability for a LED light head to change color and operate as a single, dual, or tri-color light head through user-selected color modes.

### Easy Push-Button Flash Pattern and Color Mode Selection

XStream warning lights come equipped with (25) flash patterns and (10) color modes. Flash patterns and color modes can be changed simply with two recessed buttons included on each model. Wired units use an advanced five-wire technology that coordinates flash patterns between up to eight lights at once. Accessory plug models are simple to transfer from vehicle to vehicle and include two switches for on/off and White steady-burn.



Accessory plug models include two switches for on/off and White steady-burn

**COLOR MODE**

COLOR MODE	SINGLE-HEAD	DUAL-HEAD 1	DUAL-HEAD 2	DESCRIPTION
1	Color 1, 2, 3	Color 1, 2, 3	Color 1, 2, 3	Light heads flash COLOR1, COLOR2, & COLOR3
2	Color 1	Color 1	Color 1	Light heads flash COLOR1
3	Color 2	Color 2	Color 2	Light heads flash COLOR2
4	Color 3	Color 3	Color 3	Light heads flash COLOR3
5	Color 1, 2	Color 1, 2	Color 1, 2	Light heads flash COLOR1 & COLOR2***
6	Color 1, 3	Color 1, 3	Color 1, 3	Light heads flash COLOR1 & COLOR3***
7	Color 2, 3	Color 2, 3	Color 2, 3	Light heads flash COLOR2 & COLOR3***
8	Color 1 (duplicates 2)	Color 1	Color 2	Light head 1 flashes COLOR1, Light head 2 flashes COLOR2***
9	Color 1 (duplicates 2)	Color 1	Color 3	Light head 1 flashes COLOR1, Light head 2 flashes COLOR3***
10	Color 2 (duplicates 3)	Color 2	Color 3	Light head 1 flashes COLOR2, Light head 2 flashes COLOR3***



Each model includes light head, two suction cups, bail and pivot brackets, mounting hardware and three different length snap-on flash guards.


**SPECIFICATIONS**

	SINGLE-HEAD	DUAL-HEAD
OPERATING VOLTAGE	12 Vdc	
CURRENT DRAW	0.8 A (Steady White)	1.5 A (Steady White)
OPERATING TEMP.	-40° to +176° F (-40° to +80° C)	
<b>PHYSICAL SPECIFICATIONS LIGHT HEAD</b>		
LENGTH	3.9 in (9.9 cm)	7.3 in (18.5 cm)
WIDTH	2.2 in (5.6 cm)	
HEIGHT	1.0 in (2.5 cm)	
<b>SHIP WEIGHT</b>		
	0.6 lb (0.3 kg)	1.0 lb (0.5 kg)


**FLASH PATTERNS**

PATTERN	NAME
1	Triple 92.3
2	Triple 90
3	Single 122
4	Single 75*
5	Single 90*
6	Single 113*
7	Cruise w/ Flicker
8	Random Time
9	Random Common*
10	Steady
11	Single 75*
12	Single 120*
13	Double 80*
14	Double 120*
15	Triple 80*
16	Triple 120*
17	Quad 60*
18	Quad 75*
19	Quad 95*
20	FedPulse Quad 75*
21	Quint 75*
22	7x
23	Single-Quad*
24	Decelerating
25	Accelerating

**Dual-Head Model**




**Single-Head Model**



\* Conforms to CCR Title 13

**Visor Lengths Included with Each Model**



## HOW TO ORDER

LED Color      Lens Color  
A B G R      W      C

### SINGLE-HEAD MODELS WITH WIRE LEADS

XSM1-BRW-US	Blue/Red/White
XSM1-WAG-US	White/Amber/Green
XSM1-BRA-US	Blue/Red/Amber
XSM1-BWA-US	Blue/White/Amber
XSM1-RWA-US	Red/White/Amber

### DUAL-HEAD MODELS WITH WIRE LEADS

XSM2-BRW-US	Blue/Red/White - Blue/Red/White
XSM2-WAG-US	White/Amber/Green - White/Amber/Green
XSM2-BRA-US	Blue/Red/Amber - Blue/Red/Amber
XSM2-BWA-US	Blue/White/Amber - Blue/White/Amber
XSM2-RWA-US	Red/White/Amber - Red/White/Amber

### SINGLE-HEAD MODELS WITH ACCESSORY PLUG


XSM1C-BRW-US	Blue/Red/White
XSM1C-WAG-US	White/Amber/Green
XSM1C-BWA-US	Blue/White/Amber
XSM1C-RWA-US	Red/White/Amber

### DUAL-HEAD MODELS WITH ACCESSORY PLUG

XSM2C-BRW-US	Blue/Red/White - Blue/Red/White
XSM2C-WAG-US	White/Amber/Green - White/Amber/Green
XSM2C-BWA-US	Blue/White/Amber - Blue/White/Amber
XSM2C-RWA-US	Red/White/Amber - Red/White/Amber

### ACCESSORIES

<b>XSMBKT01</b>	Visor mount kit for use with single- or dual-head models
<b>XSMBKT02</b>	Adjustable, swivel mount for single- or dual-head models
<b>XSMBKT03</b>	Headliner mount bracket for single- or dual-head models
<b>XSMBKT07</b>	Visor mount kit for use with (1) single- or dual-head XStream and (2) cameras (forward and rear facing), Dodge Charger, 2011-2022
<b>XSMBKT10</b>	Visor mount kit for use with (1) single- or dual-head XStream and (2) cameras (forward and rear facing), Ford F-150, 2015-2022, Ford F-250/350/450/550 Super Duty, 2017-2022, Ford Expedition 2018-2022
<b>XSMBKT11</b>	Visor mount kit for use with (1) single- or dual-head XStream and (2) cameras (forward and rear facing), Ford Police Interceptor Utility, 2020-2022
<b>XSMBKT12</b>	Visor mount kit for use with (1) single- or dual-head XStream and (2) cameras (forward and rear facing), Dodge Durango, 2011-2022
<b>XSMBKT13</b>	Rear window mount kit for (2) single- or dual-head XStream models, Ford Ranger, 2019-2020
<b>XSMBKT14</b>	Visor mount kit for use with (1) single- or dual-head XStream, with mounting holes for front and rear facing cameras, Chevrolet Tahoe, 2021-2022
<b>Z205003</b>	Rubber gasket



XStream, SpectraLux, and Solaris are registered trademark of Federal Signal Corporation.  
 Ford and Dodge are trademarks of their respective owners.

