



Main

Range of product	Altivar
Bus type	Modbus
Accessory / separate part category	Connection accessory
Accessory / separate part type	Line terminator
Accessory / separate part destination	RJ45 connector
Quantity per set	Set of 2

Complementary

Range compatibility	Altivar 61 Altivar 71Q Altivar Easy 310 Altivar 31 Preventa XPS MF Altivar Machine ATV320 Altivar 32 Lexium SD3 Modicon LMC058 Altivar Easy 610 Altivar 21 Zelio Logic Altivar Process ATV600 Altistart 48 Altivar Process ATV900 Modicon M258 Altivar 312 Altivar Machine ATV340 except Sercos drives Modicon M238 Altivar 61Q Altivar 31C Altistart 22 Altivar 212 Altivar 71 Altivar 12
Communication port protocol	Modbus
Terminator resistance	120 Ohm
Terminator capacitance	1 nF
Net Weight	0.44 lb(US) (0.2 kg)

Ordering and shipping details

Category	18062 - MISC. ALTIVAR/ALTISTART CABLES, CONNECTORS
Discount Schedule	CP1G
GTIN	00785901442363
Nbr. of units in pkg.	2
Package weight(Lbs)	0.02 lb(US) (0.01 kg)
Returnability	Yes
Country of origin	CN

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Package 1 Height	0.200 dm
Package 1 width	0.600 dm
Package 1 Length	0.600 dm

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------