

In most applications, a signal booster (Model Number: B122-000-60) should be used with this cable to ensure a signal strong enough for your display. An alternate solution is to use a Tripp Lite HDMI over Cat5 Extender (Model Number: B126-1A1) in place of a 50 ft. HDMI cable and signal booster.

Standard-Speed HDMI Easy Pull Cable, Digital Video with Audio (M/M), 50 ft. (15.24 m)

MODEL NUMBER: **P568-050-EZ**



Description

Tripp Lite's 50-ft. (15.24 m) Standard Speed HDMI Easy Pull All-in-One Monitor Cable makes running long length video cables a snap. The pull-apart design allows the cable to be run through conduit or other tight areas that a HDMI connector wouldn't fit through. Diameter of the circular DIN end is only 7/8". Circular Easy Pull connector is threaded to ensure maximum security once the cable is reattached. Supports iPad2 Video Mirroring when used with Apple Digital AV Adapter. HDMI assures that the best audio/video signal is always sent from the source (HDTV signal, Blu-Ray Player) to the display (Projection Television, LCD, Plasma, etc.). It does this by allowing uncompressed video and multi-channel audio data to be input to the display device through a single cable. An HDMI connection allows input at high rates of speed, up to 10.2 Gbps. In most applications, a signal booster (B122-000-60) will need to be used with this cable to ensure a signal strong enough for your display.

Features

- Two-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- Creates a pure digital connection between HDMI-enabled HDTV display devices and HDMI-enabled digital video sources
- Supports iPad2 Video Mirroring when used with Apple Digital AV Adapter
- Gold-plated connectors provide optimal signal transfer
- Premium double-shielded cable protects against outside noise (EMI/RFI)
- Impedance-matched twisted-pair construction reduces cross-talk and interference
- Bandwidth up to 10.2 Gbps - Full 1080p resolution

Highlights

- Two-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- Supports iPad2 Video Mirroring when used with Apple Digital AV Adapter
- Bandwidth up to 10.2 Gbps - Full 1080p resolution
- Standard Speed HDMI and HDCP compliant
- Supports HD Video resolutions up to 1080p

Package Includes

- Standard Speed HDMI Easy Pull Cable, 1080p, Digital Video with Audio (M/M), 50-ft. (15.24 m)



- In most applications, a signal booster (B122-000-60) will need to be used with this cable to ensure a signal strong enough for your display

Specifications

OVERVIEW	
UPC Code	037332142214
Technology	HDMI
PHYSICAL	
Color	Black
Cable Length (ft.)	50
Cable Length (m)	15.2
Shipping Dimensions (hwd / cm)	6.35 x 12.70 x 17.78
Shipping Dimensions (hwd / in.)	2.50 x 5.00 x 7.00
Shipping Weight (kg)	0.84
Shipping Weight (lbs.)	1.85
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>