# Home Care Technical Specification SecureMount Anchor SMA1000

## **Stock Numbers:**

#### SMA1000CH –SecureMount Anchors

Chrome Finish 2 Anchors

#### □ SMA1000OWB –SecureMount Anchors

Old World Bronze Finish 2 Anchors

#### □ SMA1001CH –SecureMount Anchors

Chrome Finish 10 Anchors

## □ SMA1005CH –SecureMount Anchors

Chrome Finish Single Anchor

#### **Materials:**

SecureMount Anchor mounting plate is made of stainless steel.

**SecureMount Anchor guide** and **anchor** are made of POM.

## **Compliance:**

 CSI SecureMount Anchors meet or exceed the applicable requirements of the following standards:

ADA ANSI A117.1 ASTM F446 CSA B45 CSA B651


 For use only when securely installed in approved substrates\* for persons no more than 300lbs.

\*Requires a 3½" space behind the wall and works in the following substrates

- 1/2" or 5/8 " Dry Wall
- 1/2" or 5/8 " Dry Wall with Tile
- 1/2" or 5/8 " Dry Wall with Marble
- 1/8" or 1/4" Fiberglass Tub Surround



### **Dimensions:**



#### **Installation Instructions:**

Direction for wall mounting installation:

- 1. Position grab bar on wall in desired location and mark around the outside of the flanges.
- One at a time, center the mounting plate within the marked flanges, and mark the center hole for drilling.
- 3. Drill one 11/4" hole at each mounting location.
- 4. Insert guide sleeves into each hole in the wall. (Note: UP indicator must always point up regardless of grab bar orientation)
- 5. Connect pull tab to the secure mount anchor.
- 6. With pull tab up, insert the anchor all the way into the hole in the wall.
- 7. Pull back on the pull tab, and disconnect it from the anchor.
- 8. Place mounting plate over the hole and secure with the anchor screw, and flat and rubber washers. (Note: Bar indicators should be facing in, align arrows)
- 9. Align the grab bar flanges to the secure mount anchor and secure with flange screws and split lock washer.

Directions for stud mounting installation:

- 1. Position grab bar on wall in desired location and mark around the outside of the flanges.
- 2. Determine stud center and drill one 1/8" pilot hole at each location.
- 3. Install wood screw supplied with grab bar.
- Install the 3 additional wood screws through the grab bar flange into the elongated mounting plate slots.

Stock Number:	SecureMount Anchor
By Creative Specialties	

25300 AL MOEN DRIVE • NORTH OLMSTED, OH 44070 CORPORATE HEADQUARTERS: (800) 321-8809 • FAX: (800) 848-6636 INTERNATIONAL: (440) 962-2000 • FAX: (440) 962-2726 CUSTOMER SERVICE (USA): 800-882-0116 • FAX: (888) 379-2720 WWW.MOEN.COM

©Copyright Creative Specialties International