

# PT14

## 14 DAY UV-RESISTANT SPECIALTY PAPER MASKING TAPE

### DESCRIPTION

Blue fine crepe paper masking tape with a specially formulated pressure-sensitive, synthetic rubber adhesive designed for exposure to sunlight for up to fourteen days. Exhibits easy, clean removal from most surfaces. Excellent conformability as well as smooth backing for superior paint lines and reduced fingertip abrasion. Consistent, easy unwind and resistant to humidity and paint bleed-through. Also has secure adhesion and is stain-resistant.

### PRODUCT APPLICATION

Wherever masking is exposed to weather / out-of-doors conditions, interior masking of windows (where adhesive will be directly exposed to sunlight). Protective, compatible for use on lacquer or polyurethane-coated surfaces, unfinished wood, wallpaper, or new, unpainted, or freshly painted wallboard.

### STORAGE RECOMMENDATION

Store new stock behind current stock. Store in a clean, dry place. Temperature of 70°F (21°C) +/- 6°F, and 40% to 50% relative humidity are recommended.

### SHELF LIFE

When stored under recommended conditions, converted rolls have an expected shelf life of up to one (1) year from the date of shipment. Jumbo rolls have the same expected shelf life, but it is recommended that they are converted within six (6) months of date of shipment.



100 Paramount Drive, Suite 300 | Sarasota, FL 34232 | USA  
Customer Service: 800.IPG.8273 | 800.474.8273  
Tape Technical Service: 877.447.4832  
www.itape.com | info@itape.com

While we believe them to be reliable, the statements and information herein are only for general guidance and are not warrants or guarantees for accuracy and completeness. The user must, by test or otherwise, determine suitability for this purpose. There is no warranty of fitness for a particular purpose. Our standard term and conditions of sale apply exclusively to all orders, and all liability for damages of any kind, including consequential, exceeding purchase price is excluded. No one is authorized by us to make oral warranties. We reserve the right to make changes without notice or obligation in our products and publications.

EFFECTIVE: 5/13

## INTERTAPE POLYMER GROUP® TECHNICAL DATA SHEET

### NOMINAL VALUES

The following data are nominal values based on PSTC, ASTM and other standard tests. The data should not be considered as specifications.

<b>Backing</b>	Fine Crepe Paper
<b>Adhesive</b>	Synthetic Rubber
<b>Adhesion to Steel</b> (oz/in of width)	26 (7 N/25mm)
<b>Tensile Strength</b> (lbs/in of width)	23 (101 N/25mm)
<b>Elongation</b> (% at break)	11
<b>Total Thickness</b> (mils)	5.5 (0.14mm)
<b>Quick Stick</b> (oz/in of width)	
To Kraft	4 (1.1 N/25mm)
To Steel	12 (3.3 N/25mm)
<b>Color</b>	Blue

