Coated Fiberglass Sleeve





NU-SLEEVE SG-200 is a braided fiberglass sleeve coated with a liquid silicone rubber. The braid is heat treated to optimize coating adhesion and minimize surface irregularities.

NU-SLEEVE SG-200 is an excellent electrical insulator, up to 7 kV depending on the requested dielectric strength.

NU-SLEEVE SG-200 is highly resistant to endfray and coating fractures, even when stretched over irregular shapes. It is the ideal choice for harsh environments over a wide temperature range from -70°C up to 200°C.

NU-SLEEVE SG-200 is used extensively in high temperature applications where one or more of the following features are required: flexibility, expandability, abrasion resistance, cut-through resistance and chemical resistance.

It is then well suited for automotive applications.







Characteristics & Properties

Colors: standard colors are black, white, natural (tan), red, red oxide, blue, yellow, green and orange. Other colors upon request.

Physical properties	Value
Continuous temperature of use - min/max	-70°C / 200°C (-94°F / 392°F)
Dieletric properties	up to 7 kV
Heat aging	no effect - 275°C (527°F) for 136hr
Flammability (FMVSS302)	self-extinguishing
Abrasion resistance (SAEARP1536)	2,300 cycles
	Desirtata de escribada escalas de escalas de escalidade

Chemical resistance

Resists to chemicals and automotive fluids (oils, coolant, battery liquid, brake fluid, gasoline, urea...)

Dimensions

Other dimensions available upon request.

Designation	Nominal Ø (mm)
NU-SLEEVE SG-200 03	3
NU-SLEEVE SG-200 04	4
NU-SLEEVE SG-200 05	5
NU-SLEEVE SG-200 06	6
NU-SLEEVE SG-200 07	7
NU-SLEEVE SG-200 08	8
NU-SLEEVE SG-200 10	10
NU-SLEEVE SG-200 11	11
NU-SLEEVE SG-200 13	13
NU-SLEEVE SG-200 14	14
NU-SLEEVE SG-200 16	16
NU-SLEEVE SG-200 19	19
NU-SLEEVE SG-200 22	22
NU-SLEEVE SG-200 25	25
NU-SLEEVE SG-200 29	29
NU-SLEEVE SG-200 32	32
NU-SLEEVE SG-200 38	38

Approvals

- Direct: Volkswagen.
- Via Tier-1: Caterpillar, Ford, General Motors, Jaguar/Land Rover, Nissan, Volvo Cars Corp.

Packaging

NU-SLEEVE SG-200 is delivered in spools, bulk spools or in cut lengths.

Data and photos for information only. Delfingen makes no warranties as to the accuracy or completeness of this information. Delfingen reserves the right to make changes in materials or processing without notification.