

GERSON

9500 SERIES

DROP DOWN

HALF -MASK RESPIRATOR

ADVANCED FUNCTION RESPIRATOR

The Gerson 9500 Series Drop Down half-mask respirator features the QuickDrop™ system, enhancing worker convenience and comfort. The QuickDrop™ system is engineered for easy removal of mask from face without the need to remove protective headgear or eyewear. This respirator is NIOSH Approved and compatible with Gerson replaceable cartridges and filters.



QuickDrop™ 



WORKING MODE



RELAXED MODE

2 STEP COMFORT

Advanced QuickDrop™ Function is engineered to allow drop down use without rethreading or removing headgear or eyewear.

Call Customer Service Direct: (508) 947-4000



GERSON® 9500 Series

NEXT GENERATION FEATURES



9500 SERIES NEXT GENERATION FEATURES

Drop down use without rethreading

- > Liquid silicone rubber
- > Quick 1/4 turn bayonet connection
- > Individually packaged in resealable plastic bags
- > Bonus Hygiene Guard for clean storage and product protection



Quick-Adjusting Head Straps with Robust Elastic Webbing.



Adjustable 3-Position Head Support



Quick-Adjusting Lower Head Strap Buckle & Clip



DESCRIPTION	MODEL#	PART#
Liquid Silicone Drop Down Half-Mask Respirator (sm)	9571	0879571
Liquid Silicone Drop Down Half-Mask Respirator (med)	9572	0879572
Liquid Silicone Drop Down Half-Mask Respirator (lg)	9573	0879573

PACKAGING: 1/bag, 24/case

Read and Understand Instructions and Warnings before using this product.



2 STEP COMFORT

Lower the mask to interact with your co-workers. Quick adjust clip allows you to easily put it back on without removing eyewear or headgear.




WORKING MODE
Adjust the straps to wear the mask during normal operation.



RELAXED MODE
Drop down the straps to lower the mask when moving in and out of contaminated areas.

QuickDrop™

Advanced **QuickDrop™** function system is designed for easy removal of mask from face **without rethreading** or the need to remove protective headgear or eyewear.



EASY REMOVAL FUNCTION
Simply release the straps to suspend the mask to talk to co-workers.
Try it NOW!



LOUIS M. GERSON CO., INC.

16 Commerce Blvd., Middleboro, MA 02346 USA

Phone: 508.947.4000

sales@gersonco.com • international@gersonco.com

www.gersonco.com


© 2022, Louis M. Gerson Co., Inc. All Rights Reserved.

To find out more about Gerson Company and our products, please visit www.gersonco.com



Compatible Cartridges & Filters

CARTRIDGE BEST SELLERS



GAS & VAPOR

- > **G01** - Organic Vapor
- > **G03** - Organic Vapor/Acid Gas, Organic Vapor, Sulfur Dioxide, Hydrogen Chloride, Hydrogen Fluoride



COMBINATION GAS/VAPOR & P100

- > **G71** - Organic Vapor, All Particulates



MULTI-GAS P100

- > **G78** - Ammonia, Chlorine Dioxide, Chlorine, Formaldehyde, Hydrogen Chloride, Hydrogen Fluoride, Hydrogen Sulfide, Methylamine, Organic Vapor, Sulfur Dioxide, All Particulates

PARTICULATE FILTERS



P100 CARTRIDGE

- > **GX70** - NIOSH 99.97% filter efficiency. Effective against all solid and oil particulate aerosols. With fit check port.



P100 PANCAKE

- > **XP100** - NIOSH 99.97% filter efficiency. Effective against all solid and oil particulate aerosols.



> **XP100-OV/AG** - NIOSH

- 99.97% filter efficiency. Effective against all solid and oil particulate aerosols.*

PARTICULATE FILTER PADS



P95 PARTICULATE FILTER PAD

- > **G95P** - NIOSH 95% filter efficiency. Effective against all solid and oil particulate aerosols.



FILTER PAD RETAINER

- > **172** - Filter Pad Retainer

* **WARNING:** Not NIOSH approved for ozone protection, organic vapors, or acid gases. Nuisance Level refers to concentrations not exceeding the OSHA PEL or applicable government standards for exposure limits, whichever is lower. Do not use in or around sandblasting operations. This product does not supply oxygen.

Visit www.gersonco.com for full listing of compatible cartridges and filters.