





PIG® TuffGrit™ Step Cover with Fine Grit

FLM3023 9" x 24" x 1", Install With Adhesive or Mechanical Fasteners, 1 each

Anti-slip step treads add traction in high-traffic areas, even in wet or oily conditions. Rigid fiberglass Stair Tread Covers with TuffGrit™ texture easily outperform rubber and vinyl treads, paints and tapes.

- Durable fiberglass step cover with proprietary TuffGrit™ fine texture is 0.18" thick for use in high-traffic areas
- Full-coverage design wraps around stair nosing -- where most slips occur -- and provides extended tread depth for excellent footing
- Anti-slip step tread adds reliable traction, even in wet or oily conditions, far exceeding ANSI standards
- Resists UV, chemicals, corrosion and heavy traffic for long-lasting protection, indoors or out
- Pre-cut Step Covers can be installed on steel and composite grating, steel and aluminum plate, concrete or wood (fasteners and adhesive not included)
- Available Glo Yellow option adds visibility in low-light conditions
- Ask us about custom sizes, colors and personalization



| Item# | Description | Dimensions | Weight |
|-------------|-------------|---------------------|-----------|
| FLM3023-GBY | | 9" W x 24" L x 1" H | 2.52 lbs. |
| FLM3023-GDY | | 9" W x 24" L x 1" H | 2.52 lbs. |
| FLM3023-YB | | 9" W x 24" L x 1" H | 2.52 lbs. |
| FLM3023-YW | | 9" W x 24" L x 1" H | 2.52 lbs. |

Metric Equivalent:

| Item# | Description | Dimensions | Weight |
|-------------|-------------|---------------------------|--------|
| FLM3023-GBY | | 23cm W x 61cm L x 2.5cm H | 1.1 kg |
| FLM3023-GDY | | 23cm W x 61cm L x 2.5cm H | 1.1 kg |
| FLM3023-YB | | 23cm W x 61cm L x 2.5cm H | 1.1 kg |
| FLM3023-YW | | 23cm W x 61cm L x 2.5cm H | 1.1 kg |

Specifications

| | |
|-------------------|---------------------|
| Dimensions | 9" W x 24" L x 1" H |
| Brand | PIG |

| | |
|----------------------------|----------------------------------|
| Installation Method | Adhesive or Mechanical Fasteners |
| Sold as | 1 each |
| Weight | 2.52 lbs. |
| Composition | Fiberglass Aluminum Oxide |
| UNSPSC | 30162104 |

Metric Equivalent

| | |
|-------------------|---------------------------|
| Weight | 1.1 kg |
| Dimensions | 23cm W x 61cm L x 2.5cm H |

Technical Information

US Only

This product can ONLY be shipped to the United States.

Certifications, Approvals and Ratings

NFSI Certified



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com