





PIG® TuffGrit™ Step Cover with Extra Coarse Grit

FLM3024 9" x 30" x 1", Install With Adhesive or Mechanical Fasteners, 1 each

Anti-slip step treads add traction in rugged environments, even in wet or oily conditions. Rigid fiberglass Stair Tread Covers with TuffGrit™ texture easily outperform rubber and vinyl treads, paints and tapes.

- Durable fiberglass step cover with proprietary TuffGrit™ extra coarse texture is 0.26" thick for use in high-traffic areas or heavy industrial environments
- Full-coverage design wraps around stair nosing -- where most slips occur -- and provides extended tread depth for excellent footing
- Aggressive anti-slip step tread adds reliable traction, even in wet or oily conditions, far exceeding ANSI standards
- Resists UV, chemicals, corrosion and heavy traffic for long-lasting protection, indoors or out
- Pre-cut Step Covers can be installed on steel and composite grating, steel and aluminum plate, concrete or wood (fasteners and adhesive not included)
- Available Glo Yellow option adds visibility in low-light conditions
- Ask us about custom sizes, colors and personalization



Item#	Description	Dimensions	Weight
FLM3024-GBY		9" W x 30" L x 1" H	3.95 lbs.
FLM3024-GDY		9" W x 30" L x 1" H	3.95 lbs.
FLM3024-YB		9" W x 30" L x 1" H	3.95 lbs.
FLM3024-YW		9" W x 30" L x 1" H	3.95 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
FLM3024-GBY		23cm W x 76cm L x 2.5cm H	1.8 kg
FLM3024-GDY		23cm W x 76cm L x 2.5cm H	1.8 kg
FLM3024-YB		23cm W x 76cm L x 2.5cm H	1.8 kg
FLM3024-YW		23cm W x 76cm L x 2.5cm H	1.8 kg

Specifications

Dimensions

9" W x 30" L x 1" H

Brand	PIG
Installation Method	Adhesive or Mechanical Fasteners
Sold as	1 each
Weight	3.95 lbs.
Composition	Fiberglass Aluminum Oxide
UNSPSC	30162104

Metric Equivalent

Weight	1.8 kg
Dimensions	23cm W x 76cm L x 2.5cm H

Technical Information

US Only

This product can ONLY be shipped to the United States.

Certifications, Approvals and Ratings

NFSI Certified



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com