

PIG® Oil-Only Barrel Top Absorbent Mat with Poly Backing



MAT1501 Heavyweight, For 55 gal. drums with 2 bungs (.75" Dia. and 2" Dia.), 25 pads per box

Absorb and trap oil that drips, leaks or spills from your pump onto the top of your dual-bung drum using these perfect-fit mat pads with poly backing.

- Keep the oil in 55-gallon drums from making a mess
- Drum pads are made to fit around both bungs of any standard 55-gallon steel drums and to catch oil drips during and after pumping
- Poly backing won't let hard-to-clean liquids penetrate and reach your barrel
- Heavyweight mats are built to last without ripping, tearing or falling apart, even when saturated
- Soak up any fuels, oils or oil-based liquids; oil-only mats do NOT absorb water
- Box can be conveniently wall-mounted to make storing and dispensing easy; wall-mount hardware not included
- Can be wrung out and incinerated after use to reduce waste or for fuels blending
- Mats take on the properties of absorbed liquids; always take proper precautions when handling saturated absorbents



Specifications

| | |
|------------------|--|
| Absorbency Range | 1 - 9.9 gal. |
| Use With | 55 gal. drums with 2 bungs (.75" Dia. and 2" Dia.) |
| Dimensions | ext. dia. 22" |
| Mat Weight | Heavyweight |
| Absorbency | Up to 6.9 gal. per box |
| Absorbency per | Up to 35.35 oz. per pad |
| Color | White |
| Brand | PIG |
| Bung Opening | .75" & 2" |
| Category | Barrel Top Absorbent Mat |
| Drum Type | Steel Drum |

| | |
|------------------------------------|---|
| Drum Size | 55 gal. |
| Flammability Specifications | Flame Resistant - Will melt and self-extinguish |
| Fluid Absorbed | Oils; Fuels; Oil-Based Liquids (Not Water) |
| Indoor/Outdoor | Indoor Use; Short-Term Outdoor Use |
| Incinerable | Yes |
| Reusable | No |
| Special Feature | Poly-Backing |
| Static-Dissipative | No |
| UV Resistant | No |
| Wringable | No |
| Sold as | 25 pads per box |
| Weight | 7 lbs. |
| # per Pallet | 72 |
| Composition | Polypropylene |
| UNSPSC | 47131901 |
| Pigalog® Page Number | <u>Page N7</u> |

Metric Equivalent

| | |
|-----------------------|----------------------|
| Absorbency per | Up to 1 L per pad |
| Absorbency | Up to 26.1 L per box |
| Weight | 3.2 kg |
| Dimensions | ext. dia. 56cm |

Technical Information

Technical Documents

SPCC: 8 Things You Need to Know

Technical Data Sheet for PIG® Oil Only Absorbents

29 CFR 1910.22(a)(2)

40 CFR 112.7

40 CFR 122.26



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com

