

PIG® HazMat Chemical Barrel Top Absorbent Mat

MAT1504 Lightweight, For 55 gal. drums with 2 bungs (2" Dia.), 25 pads per box

Safely soak up hazardous chemicals that drip from the pump on your barrel with this drum-top mat pad designed to fit perfectly around both bungs.

- Absorbs acids, bases, corrosives and chemicals that drip or spill from the pump on top of your drum
- Chemical absorbent mat pads are made to fit around the double bungs on top of 55-gallon steel or poly drums
- Chemical-resistant mat won't degrade or cause a dangerous reaction upon contact with corrosive spills
- Pink color is easily distinguishable to help ensure that workers use the correct mat for chemicals
- Lightweight mats are built to last without ripping, tearing or falling apart, even when saturated
- Convenient box can be mounted to the wall for easy dispensing and storage; wall-mount hardware not included
- Mats take on the properties of absorbed liquids; always take proper precautions when handling saturated absorbents



Specifications

Absorbency Range	1 - 9.9 gal.
Use With	55 gal. drums with 2 bungs (2" Dia.)
Dimensions	ext. dia. 22"
Mat Weight	Lightweight
Absorbency	Up to 3.31 gal. per box
Absorbency per	Up to 16.94 oz. per pad
Color	Pink
Brand	PIG
Bung Opening	2" & 2"
Category	Barrel Top Absorbent Mat
Drum Type	Steel Drum; Poly Drum

Drum Size	55 gal.
Flammability Specifications	Flame Resistant - Will melt and self-extinguish
Fluid Absorbed	Acids; Bases; Unknowns
Indoor/Outdoor	Indoor Use
Incinerable	Yes
Reusable	No
Static-Dissipative	No
UV Resistant	No
Wringable	No
Sold as	25 pads per box
Weight	3.6 lbs.
# per Pallet	72
Composition	Polypropylene
UNSPSC	47131901
Pigalog® Page Number	<u>Page 69</u>

Metric Equivalent

Absorbency per	Up to 500.9 mL per pad
Absorbency	Up to 12.5 L per box
Weight	1.6 kg
Dimensions	ext. dia. 56cm

Technical Information

Technical Documents

[PIG Hazardous Chemical Absorbents](#)

[Technical Data Sheet for PIG® HazMat Absorbents](#)

[29 CFR 1910.22\(a\)\(2\)](#)



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com