

# MAC FAUCETS

## *Electronic, Sensor Liquid Soap Dispenser*



### **PYOS-1205** **MATCHING FAUCET** **FA400-1205**

#### **Features:**

- **Dispenses Standard liquid Soap.**
- **Soap Amount is Adjustable.**
- **Noise Free Reliable Operation.**
- **Battery Powered, AC Optional.**
- **Easy to Refill Soap System Design.**
- **Available in Twenty + Matching finishes**

#### **Package Includes**

*Spout*

*Soap Pump*

*All Hose Connections between Pump and Spout*

*800ml Soap Bottle*

*Battery Case and Case Holder*

*Mounting Hardware*

*Remote Control Optional*

*All hardware necessary for satisfactory installation*

**DESIGNED  
& ASSEMBLED IN**  
  
**U.S.A.**





***BEST SUITED FOR VESSEL SINK APPLICATIONS WHERE THE TOP OF THE SINK IS 5" ABOVE THE COUNTERTOP SURFACE***

SPECIFICATIONS	
MODEL:	<b>PYOS-1205</b>
SPOUT:	<b>BRASS</b>
POWER:	<b>4 (D) BATTERIES / AC ADAPTER OPTIONAL</b>
SOAP PUMP:	<b>6 VOLT NOISE-FREE PERISTALTIC PUMP SYSTEM</b>
COUNTER ACCOMMODATIONS:	<b>PLEASE VIEW ROUGH-IN DRAWINGS ON PAGE TWO</b>
SENSOR TYPE:	<b>ACTIVE INFRARED, SELF-ADJUSTING</b>
SENSING RANGE:	<b>ADJUSTABLE WITH <u>OPTIONAL REMOTE CONTROL</u></b>
WORKING SOAP:	<b>STANDARD LIQUID SOAP. NO GRIT (INDUSTRIAL) SOAP</b>
SOAP BOTTLE CAPACITY:	<b>800ML (JUST UNDER A QUART) <u>OPTIONAL 1 GALLON CONTAINERS</u></b>
SOAP AMOUNT PER USE:	<b>0.5ML TO 1.5ML, ADJUSTABLE WITH <u>OPTIONAL REMOTE CONTROL</u></b>

All Dimensions  
in Inches

Battery Cable: 45"  
Sensor Cable: 32"  
Soap Hose: 32"



**Maximum Counter Top Thickness 2"**

**Optional Equipment:**

- AC Adapter
- Remote Control (one for many dispensers)
- 1 Gallon capacity container.

MAC FAUCETS, LLC

www.macfaucets.com Tel 866 558 3200 Fax 310 919 3073 Email Info@macfaucets.com