



ITEM	PART #	DESCRIPTION	R/Q	QTY
1	17-0004	QC 3/8FX3/8 SOCKET BRASS		1
2	15-0341	HOSE-3/8" x 33' 4000 PSI		1
3	24-0105	ELBOW 90°- STEEL - 3/8M x 3/8F		2
4	22-0491	3 WAY BALL VALVE - 3/8" FNPT 7350PSI		1
5	15-0342	HIGH PRESSURE HOSE - 1/4" X 27.5" 4000 PSI	X	1
6	30-3158	HEX NYLON LOCKNUT-ZINC M4-0.7		2
7	27-8032	HHCS-ZI GR 8.8 M8-1.25P X 20MM		4
8	28-0003	WASHER-ZI SAE TYPE A 5/16"		8
9	20-1385A77	RIGHT AXLE BRACKET		1
10	28-0008	WASHER-ZI SAE TYPE A 5/8"		2
11	14-0139	WHEEL-10" RUBBR-SOLID GREY RIM		2
12	33-0351	COLLAR - 5/8" I.D. STEEL		2
13	30-3156	HEX NYLON LOCKNUT M8 X 1.25P X 6mm		4
14	14-0144	VIB/ISO 30mm X 40mm HEIGHT		2
15	27-8065	HHCS-ZI GR8.8 M8-1.25 X 12MM		2
16	29-0007	LOCKWASHER-ZINC MED 5/16		2
17	30-3160	HEX NYLON LOCKNUT-ZINC M12-1.75		2
18	28-0006	WASHER - ZI SAE TYPE A 1/2		6
19	14-0141	CASTORS 75mm x 25mm		2
20	27-8501	HHCS-ZI GR 8.8 M12-1.25 X 35MM		2
21	5-0339A77	FRAME - DPW2500		1
22	20-1386A77	LEFT AXLE BRACKET		1
23	15-0007	HOSE 1/2 250psi	1.75'	1
24	42-0011	SS WORM CLAMP 3/8"-1"		1
25	23-0120	HOSE BARB 1/4" M NPT x 1/2" - BRASS		1
26	42-0059	CLIP-SPRING WAND HOLDER		1
27	27-2770	PPHMS M4-0.7X16MM - SS		2
28	23-0047	COUPLING 1/4F X 3/8F HEX BRASS		1
29	23-0096	SWIVEL - 3/8 M x 3/4 F GARDEN HOSE - BRASS		1
30	15-0194	HOSE 3/8X24" 4500PSI R2 BLACK		1
31	20-1384A77	VALVE BRACKET		1
32	29-0006	LOCK WASHER - 1/4"		4
33	27-8001	BOLT - HHCS M6 - 1.00P x 15mm		4

M:\Drawings\PRIVATE LABEL\MAKINEX\DPW-2500\DPW-2500 FRAME ASSY.iam

## Mi-T-M Corporation

SCALE: NTS	DATE: 6/26/20	DRAWING SIZE: B	APPD:
<b>DPW-2500 FRAME ASSY</b>			
DRAWING/PART NO: DPW-2500 FRAME ASSY			

DRAWN BY: ATL