



## PIG® Magnetic Roof Leak Diverter Tarp

TLS1999 5' x 5', Leak Diverter Tarp, Install With Magnets

Quickly respond to metal roof and ceiling leaks with a customizable, magnetic fit, even in hard-to-access areas

- Easily keep rain and snow from storming *inside*. Whether condensation and ice, or heavy rain from a high-wind hurricane, this solution will quickly protect your team and what you've built.
- Sewn-in magnets allow for easy, fast deployment anywhere that metal is present
- Magnets provide a customized fit in areas where traditional leak diverter tarps may be difficult to hang
- Heavy-duty vinyl-coated tarp resists punctures, UV and mildew and lasts multiple deployments
- Pinched corners create a funnel to channel liquids to a drain or collection container without overflowing or sagging; engineered with leak-proof seams and connections
- Diverter tarp can hold up to 50 lbs. or 6 gallons using magnets alone; grommets along the sides provide extra support in high-flow situations
- Flow rate of 3.33 gallons per minute when used with a 1/2" ID hose
- Hose (required), hanging straps (optional) and collection container (optional) sold separately

Item#	Description	Dimensions	Weight
TLS1999-BK		5' W x 5' L	3.01 lbs.
TLS1999-WH		5' W x 5' L	3.01 lbs.
TLS1999-YW		5' W x 5' L	3.01 lbs.

### Metric Equivalent:

Item#	Description	Dimensions	Weight
TLS1999-BK		152cm W x 152cm L	1.4 kg
TLS1999-WH		152cm W x 152cm L	1.4 kg
TLS1999-YW		152cm W x 152cm L	1.4 kg

### Specifications

<b>Style</b>	Complete Kit
<b>Dimensions</b>	5' W x 5' L
<b>Application</b>	Roofs; Pipes
<b>Brand</b>	PIG

<b>Contains</b>	Leak Diverter Tarp
<b>Drainage Hose</b>	Sold Separately
<b>Flow Rate</b>	3.33 gal./Minute
<b>Hanging Straps</b>	Not Required
<b>Hose Connector</b>	.75" w/ Quick Connect
<b>Installation Method</b>	Magnets
<b>Shape</b>	Square
<b>Sold as</b>	1 each
<b>Weight</b>	3.01 lbs.
<b>Composition</b>	Diverter (Colors): PVC, Polyester Leak Diverter (Clear): PVC w/ Polyester Reinforcement Magnets: Neodymium Grommets: Brass
<b>Includes</b>	1 - 5' W x 5' L Leak Diverter Tarp 1 - Hose Connector Replacement Set (TLS745)
<b>UNSPSC</b>	24141506
<b>Pigalog® Page Number</b>	<a href="#">Page 248</a>

## Metric Equivalent

<b>Weight</b>	1.4 kg
<b>Dimensions</b>	152cm W x 152cm L

## Technical Information

### Technical Documents

[Instructions for PIG Magnetic Leak Diverter Systems](#)



**One Pork Avenue • Tipton, PA 16684-0304**

1-855-493-4647 • Fax: 1-800-621-7447 • [newpig.com](http://newpig.com) • [hothogs@newpig.com](mailto:hothogs@newpig.com)