



PIG® TuffGrit™ Diamond Plate Anti-Fatigue Mat

FLM8501 Light Drip and Overspray Applications; Dry Applications, Cushion: Vinyl & PVC Foam/Top Coat: Aluminum Oxide and Proprietary Sealant, 2' x 3'

Grit so tough it lasts 11X longer! The TuffGrit™ surface on our Diamond Plate Anti-Fatigue Mat easily outlasts the competition, providing long-lasting traction in slippery environments.

- Proprietary TuffGrit™ coating is incredibly durable and abrasion resistant; lasts up to eleven times longer than the leading competitor's grit coating in dry environments, and up to seven times longer under oily conditions
- Exceeds ANSI standards for high slip resistance, providing extreme traction even in wet areas or applications with light overspray or oily drips (not for use in standing water/oil)
- Engineered to leave no grit behind; safer than other mats that gradually lose their grit -- and their effectiveness -- over time
- Raised diamond plate texture adds a second level of slip resistance in addition to TuffGrit™ coating
- More than a half inch of PVC foam relieves stress on knees, feet, ankles and back from extended standing
- Reinforced industrial grade construction is built to last in heavy-duty applications
- Built-in beveled edges create a safe transition on and off mat

Item#	Description	Dimensions	Weight
FLM8501-BK		2' W x 3' L x .563" H	10 lbs.
FLM8501-BWY		2' W x 3' L x .563" H	10 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
FLM8501-BK		61cm W x 91cm L x 1.4cm H	4.5 kg
FLM8501-BWY		61cm W x 91cm L x 1.4cm H	4.5 kg

Specifications

Size	2' x 3'
Dimensions	2' W x 3' L x .563" H

Chemical Contact	For Light Chemical Splash
Oil/Grease Contact	For Light Oil/Grease Splash
Anti-Slip	Yes
Application	Light Drip and Overspray Applications; Dry Applications
Beveled Edge	Yes
Brand	PIG
Drainage Holes	Without Holes
Grit Surface	Yes
Safe for Welding Areas	No
Static-Dissipative	No
Sold as	1 each
Weight	10 lbs.
Composition	Cushion: Vinyl & PVC Foam Top Coat: Aluminum Oxide and Proprietary Sealant
UNSPSC	52101510

Metric Equivalent

Weight	4.5 kg
Dimensions	61cm W x 91cm L x 1.4cm H

Technical Information

Technical Documents

[PIG Anti-Fatigue Mat](#)

[Instructions for PIG Anti-Fatigue Matting](#)



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com