

NTM-52

6" BR/PAR30 Gimbal Ring with Metal Trim

Type

Project

Catalog No.

Notes

FEATURES

Trim: Adjustable metal gimbal ring can be adjusted up to 30°.

Mounting: Trim includes two "V" torsion springs to mount trim securely to housing. Replacement "V" torsion springs are available (NRA-86). Remove socket from socket plate within housing (if applicable), and mount lamp into gimbal ring.

COMPATIBLE HOUSINGS

Compatible with line voltage and sloped line voltage housings. See individual specification sheets for more information.

LAMP

Line Voltage:

· 75W BR/PAR30 Maximum (NFBIC-6INCATA; NHIC-17/100DWQA; NHIC-17QAT; NHIC-17QNBAT; NHRIC-17QAT; NHRIC-17QNBAT; NH-26Q; NH-26QNB; NHR-26Q; NH-27Q; NHIC-27QAT; NHR-27Q; NHRIC-27QAT)

Sloped Line Voltage:

· 75W BR/PAR30 Maximum (NHIC-926QAT; NHRIC-926QAT; NHIC-926DWQAT)

LABELS AND LISTINGS

cULus Listed for Damp Location when used with compatible housing.




PRODUCT IMAGES & DIMENSIONS



NTM-52BZ



NTM-52W



7-5/8"

6" BR/PAR30 Gimbal Ring with Metal Trim

Catalog No.

NTM-52BZ = 6" BR/PAR30 Gimbal Ring, Bronze finish

NTM-52W = 6" BR/PAR30 Gimbal Ring, White finish

Compatible Housings

Catalog No.

NFBIC-6INCATA = ICAT Fire Rated New Construction / 75W Max

NH-26Q = Non-IC New Construction / 75W Max

NH-26QNB = Non-IC New Construction, No Bracket / 75W Max

NH-27Q = Non-IC Shallow New Construction Housing / 75W Max

NHIC-17/100DWQA = ICAT Double Wall New Construction / 75W Max

NHIC-17QAT = ICAT New Construction / 75W Max

NHIC-17QNBAT = ICAT Shallow New Construction, No Bracket / 75W Max

NHIC-27QAT = ICAT Shallow New Construction / 75W Max

NHR-26Q = Non-IC Remodel / 75W Max

NHR-27Q = Non-IC Shallow Remodel / 75W Max

NHRIC-17QAT = ICAT Shallow Remodel / 75W Max

NHRIC-17QNBAT = ICAT Shallow Remodel, No Bracket / 75W Max

NHRIC-27QAT = ICAT Shallow Remodel / 75W Max

NHIC-926DWQAT = ICAT Double Wall New Construction Sloped / 75W Max

NHIC-926QAT = ICAT Shallow New Construction Sloped / 75W Max

NHRIC-926QAT = ICAT Shallow Remodel Sloped / 75W Max

Example: **NTM-52B** = 6" BR/PAR30 Gimbal Ring, Black finish