

PIG® Absorbent Barrel Top Safety Message Mat with Poly Backing

SGN1207 Keep Drum Top Clear, For 55 gal. drums with 2 bungs (.75" Dia. and 2" Dia.), 25 pads per box

Convey critical alerts and keep your steel drum tops clean with these leak-proof message mats.

- Barrel-top message mats warn or direct workers, beyond just drum contents, while also preventing dirty drum tops
- Ideal for chemical companies, waste facilities, manufacturing plants and other industrial setting
- Fit standard steel drums with perfectly sized cutouts for bungs
- Absorb drips, drops and spills
- Leak-proof poly-backing blocks seeping liquids to prevent dirty drums
- Bright imagery is easily legible and stands out to give you confidence that the message will be noticed
- Top location of message remains visible even when drums are grouped in storage with sides covered by other drums
- Messages can convey more than just contents of drum thanks to New Pig's printing capability, the first of its kind in the Absorbents industry
- Durable construction of heavyweight mat lasts over many uses
- Mats take on the properties of absorbed liquids, so always take proper precautions when handling saturated absorbents



Specifications

| | |
|------------------|--|
| Absorbency Range | 1 - 9.9 gal. |
| Use With | 55 gal. drums with 2 bungs (.75" Dia. and 2" Dia.) |
| Dimensions | ext. dia. 22" |
| Mat Weight | Heavyweight |
| Absorbency | Up to 6.9 gal. per box |
| Absorbency per | Up to 35.35 oz. per pad |
| Brand | PIG |

| | |
|------------------------------------|---|
| Bung Opening | .75" & 2" |
| Category | Barrel Top Absorbent Mat Sign |
| Drum Type | Steel Drum |
| Drum Size | 55 gal. |
| Flammability Specifications | Flame Resistant - Will melt and self-extinguish |
| Fluid Absorbed | Oils; Coolants; Solvents; Water; Universal |
| Indoor/Outdoor | Indoor Use |
| Incinerable | Yes |
| Legend | Keep Drum Top Clear |
| Reusable | No |
| Special Feature | Poly-Backing |
| Static-Dissipative | No |
| UV Resistant | No |
| Wringable | Yes |
| Sold as | 25 pads per box |
| Weight | 7.75 lbs. |
| # per Pallet | 72 |
| Composition | Polypropylene |
| UNSPSC | 47131901 |

Metric Equivalent

| | |
|-----------------------|----------------------|
| Absorbency per | Up to 1 L per pad |
| Absorbency | Up to 26.1 L per box |
| Weight | 3.5 kg |
| Dimensions | ext. dia. 56cm |

Technical Information



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com