

NE-700LEDRC

Dual Head LED Emergency Light with Remote Capability

Source: 1W LED

100lm per head

Type _____

Project _____

Catalog No. _____

Notes _____

PRODUCT DESCRIPTION

Mini profile LED emergency light with remote capability and self diagnostics. Luminaire provides 90 minutes of light from two adjustable heads for illuminating paths of egress upon failure of normal power.

FEATURES

- Plastic enclosure with 5VA flame retardant
- Snap-together design for easy installation
- Two fully adjustable glare-free square shape heads
- Test switch and charge rate indicator
- Maintenance-free, rechargeable Ni-Cad batteries
- Extra 3.6V battery for 3W remote capabilities
- Self-diagnostic and self-testing unit
- Ceiling or wall mounted
- Universal 120-277V input

HOUSING

Injection-molded thermoplastic ABS housing. Plastic enclosure with 5VA flame retardant. Snap-together design for easy installation. Two fully adjustable glare-free square heads for emergency lighting

ELECTRICAL

Input Voltage: 120/277 VAC 60Hz

Lumens / Wattage: (2) 100lm / 1W

Color Temperature: 6000K

Operating Temp.: 10°C to 40°C ambient temperature

Batteries: (2) NiCad 3.6V 3W maintenance-free

OPERATION

Luminaire will operate for a minimum of 90 minutes during a loss of power with a 24 hour maximum recharge time per battery.

REMOTE CAPABILITY

Luminaire includes an additional 3.6V / 3W battery. Additional battery is used to power an additional remote emergency light. Upon power failure, additional battery requires an additional 24 hours to recharge.

MOUNTING

Plastic enclosure includes a top and side knockout for conduit applications. Suitable for wall mount or ceiling mount.

LABELS AND LISTINGS



- 3 year hour limited warranty
- cULus Listed for damp locations
- cULus Listed and meets or exceeds all requirements in NFPA 70, NFPA 101 life safety code



PRODUCT IMAGES AND DIMENSIONS



NE-700LEDRC



NEG-50

Dual Head LED Emergency Light with Remote Control Capability

Catalog No. _____

NE-700LEDRCB = 2W / 200lm Dual Head LED Emergency Light with Remote Capability, Black

NE-700LEDRCW = 2W / 200lm Dual Head LED Emergency Light with Remote Capability, White

Accessories

Catalog No. _____

NEG-50 = Wet Location / Vandal Resistant Enclosure

Example: **NE-700LEDRCW** - 2W / 200lm Dual Head LED Emergency Light with Remote Capability, White