

PT-ABL-R-PTP-0-3CP

Architectural Round Post-top Style Bollard with CCT and Wattage Selector

Catalog Number: Project Name: Note: Date: Type:

Portor Lighting elevates your outdoor spaces with our Bollard Style Lighting. A perfect blend of functionality and aesthetics, our bollard lights bring safety, ambiance, and architectural charm. Experience modern illumination designed to enhance your surroundings, guiding your way with a touch of elegance.

Ideal use for walkways, entrance ways, drives and other small-area lighting applications where low mounting heights are desirable.



CONSTRUCTION

Die-cast aluminum body combined with state of the art heat dissipation. Waterproof, built rugged for outdoor harsh conditions.

ELECTRICAL

Built with the highest quality, long lasting Universal Voltage driver 120V-27V.

MOUNTING

Anchor bolt included, require assembly.

SENSOR READY

Photocell and motion sensor available.

ENERGY SAVINGS

Over 70% energy savings than traditional fixtures, low heat productions requires less maintenance and operation cost.

LISTING

UL Listed, IP65 rated, DLC Listed

WARRANTY

5 year Limited Warranty









WATTAGE	DELIVERED LUMENS	EFFICACY
14W	1727	124 lm/W
19W	2300	121 lm/W
24W	2758	123 lm/W

Based on 3000K setting. Actual lumens may vary.

TECHNICAL SPECIFICATION

ССТ	3000K/4000K/5000K
CRI	70+
DIMMABLE	0-10V dimmable
VOLTAGE	120V-277V
SENSOR	Photocell and motion sensor capable
POWER FACTOR	>0.9
SURGE PROTECTOR	4KV
WORKING TEMPERATURE	-40°F ~ 113°F
IP RATING	IP65 Wet Location
WARRANTY	5 year limited

ORDERING SAMPLE: PT-ABL-R-PTP-0-3CP

Complete Series	Shape	Тор	Style	CCT/Wattage	Lumen	Lumen/Watt	Finish
PT-ABL Architectural Bollard	R (Round)	PTP (Post Top)	0 (Open)	3CP (30K/40K/50K) (14W/19W/24W)	1727/2300/2758 Lm	123Lm/W	Bronze

www.portorlighting.com





PT-ABL-R-PTP-0-3CP

Architectural Round Post-top Style Bollard with CCT and Wattage Selector


Note: Date: Project Name: Type: Catalog Number:

DIMENSION

QTY/CARTON



PIECES





Anchor Bolt Require assembly (Included)

EM BATTERY OPTION



EM EM Battery Back-up (Actual image may vary)



DLC LISTING

CATALOG NUMBER	WATTAGE	DELIVERED LUMENS	EFFICACY	DLC PRODUCT ID	CLASSIFICATION	
PT-ABL-R-PTP-0-3CP	14W	1727	124 lm/W		PREMIUM	
	19W	2300	121 lm/W	S-8LAEUO		
	24W	2758	123 lm/W			