



# ANNIHILATORS & EXHUMERS

**AN14**  
**14 IN. ANNIHILATOR® WRECKING BAR**



**AN18**  
**18 IN. ANNIHILATOR® WRECKING BAR**



- Steel
- Demolition hammer with drywall rip axe
- Board claw to adjust wood and drywall
- Chisel
- Wrench
- Nail puller
- Wire stripper
- Bottle opener
- Rubber grip
- Total length: 14 in.

- Steel
- Demolition hammer with drywall rip axe
- Board claw to adjust wood and drywall
- Chisel
- Wrench
- Nail puller
- Wire stripper
- Bottle opener
- Rubber grip
- Total length: 18 in.


**EX8**  
**EXHUMER® 8 NAIL PULLER**



**EX9**  
**EXHUMER® 9 NAIL PULLER**



**EX9CL**  
**CLASSIC EXHUMER® NAIL PULLER**



- Steel
- Dual nail picks
- Built-in saw blade wrench
- Nail extractor for embedded nails
- Bottle opener
- Total weight: 0.9 lbs.
- Total length: 8.6 in.

- Steel
- Dual nail picks
- Built-in saw blade wrench
- Nail extractor for embedded nails
- Bottle opener
- Total weight: 1.2 lbs.
- Total length: 10.6 in.

- Steel
- Dual nail picks
- Built-in saw blade wrench
- Bottle opener
- Total weight: 0.8 lbs.
- Total length: 10.5 in.

APPLIES TO ALL PRODUCTS IN THIS DOCUMENT:



WARNING: This product can expose you to di(2-ethylhexyl)phthalate (DEHP), which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).



# GRAPHITE & STEEL HAMMERS

## D016-GS 16 OZ. GRAPHITE HAMMER



- Steel head and graphite core handle
- Diamond textured rubber grip
- Curved claw with nail puller
- Curved handle
- Smooth face
- Magnetic nail set
- Head weight: 16 oz.
- Total length: 13 in.

## D021 21 OZ. INVESTMENT CAST WOOD HAMMER – STRAIGHT HANDLE



- S-7 investment cast head and hickory handle
- S-7 investment cast head is designed for shock resistance, wide temperature range, and durability
- Straight claw with nail puller
- Straight handle
- Milled face
- Magnetic nail set
- Head weight: 21 oz.
- Total length: 18 in.

## D021C 21 OZ. INVESTMENT CAST WOOD HAMMER – CURVED HANDLE



- S-7 investment cast head and hickory handle
- S-7 investment cast head is designed for shock resistance, wide temperature range, and durability
- Straight claw with nail puller
- Curved handle
- Milled face
- Magnetic nail set
- Head weight: 21 oz.
- Total length: 18 in.

## D0S22S 22 OZ. STEEL HAMMER – SMOOTH FACE 16 INCH HANDLE



- Smooth face
- Zero Vibe design reduces strike vibration
- I-Beam shaft increases shaft length and also includes a magnetic nail set and nail puller behind hammer head
- 22 oz. head weight
- 16 in. overall length

## D0S22S-HD 22 OZ. STEEL HAMMER – SMOOTH FACE



- Steel
- Zero Vibe design reduces strike vibration
- I-beam shaft prevents bending and withstands stress
- Straight claw with nail puller
- Straight handle
- Smooth face
- Magnetic nail set
- Head weight: 22 oz.
- Total length: 18 in.

## D0S22M-HD 22 OZ. STEEL HAMMER – MILLED FACE



- Steel
- Zero Vibe design reduces strike vibration
- I-beam shaft prevents bending and withstands stress
- Straight claw with nail puller
- Straight handle
- Milled face
- Magnetic nail set
- Head weight: 22 oz.
- Total length: 18 in.

APPLIES TO ALL PRODUCTS IN THIS DOCUMENT:



WARNING: This product can expose you to di(2-ethylhexyl)phthalate (DEHP), which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).





MODEL NUMBER	ITEM DESCRIPTION	CASE PACK
<b>ANNIHILATORS &amp; EXHUMERS</b>		
AN14	14 in. Annihilator® Wrecking Bar	4
AN18	18 in. Annihilator® Wrecking Bar	4
EX8	Exhumer® 8 Nail Puller	6
EX9	Exhumer® 9 Nail Puller	6
EX9CL	Classic Exhumer® Nail Puller	6
<b>GRAPHITE HAMMERS</b>		
D016-GS	16 oz. Graphite Hammer	4
<b>STEEL HAMMERS</b>		
D021	21 oz. Investment Cast Wood Hammer - Straight Handle	4
D021C	21 oz. Investment Cast Wood Hammer - Curved Handle	4
D0S22S	22 oz. Steel Hammer - Smooth Face 16 in. Handle	4
D0S22S-HD	22 oz. Steel Hammer - Smooth Face	4
D0S22M-HD	22 oz. Steel Hammer - Milled Face	4

APPLIES TO ALL PRODUCTS IN THIS DOCUMENT:

 WARNING: This product can expose you to di(2-ethylhexyl)phthalate (DEHP), which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).