SATCO" NUVO

Project Name

Location

Prepared By



NUVO 65-781R2

LED UFO HIGHBAY 100W/4000K

Notes

www] 11-20-2023 01:02:45

Status	Active
Fixture Type	UFO Hi-Bay
Finish	Black
Wattage	100W
Lumen Output	14000L
CCT (Kelvin)	4000K
IP Rating	IP65
Indoor or Outdoor Fixture	Indoor
Specifications	
Technology	LED
Color Temperature	Cool White
CRI	80
Voltage	120V-277V
Beam Angle	90
Rated Hours	50000
Operating Temperature	-40C (-40F) to +50C (+122F)
Dimmable	Yes-Dimmable
Dimming Note	0-10V Dimming Only
Photocell or Sensor	Optional Add-On
Lens Material	Polycarbonate (PC)
Surge Protection	Built-in surge protection - 6KV
Weight (lb.)	4.53
Material	Die-cast Aluminum
Dimensions	
Height (in.)	8.11
Width (in.)	11.02
Compliance	
	cULus - Listed
Safety Listing	COLUS - LISIED
Location Rating	Wet
Location Rating Energy Star	Wet No
Location Rating Energy Star DLC Approved	Wet No Yes
Location Rating Energy Star DLC Approved DLC ID	Wet No Yes S-U80D4A
Location Rating Energy Star DLC Approved DLC ID	Wet No Yes S-U80D4A Yes
Location Rating Energy Star DLC Approved DLC ID	Wet No Yes S-U80D4A
Location Rating Energy Star DLC Approved DLC ID NSF Approved CA T20 / T24 Rationale	Wet No Yes S-U80D4A Yes T20 Exempt - Fixtures Not
Location Rating Energy Star DLC Approved DLC ID NSF Approved	Wet No Yes S-U80D4A Yes T20 Exempt - Fixtures Not Regulated
Location Rating Energy Star DLC Approved DLC ID NSF Approved CA T20 / T24 Rationale California Status Title 20 / 24 Status	Wet No Yes S-U80D4A Yes T20 Exempt - Fixtures Not Regulated Lawful for sale in California
Location Rating Energy Star DLC Approved DLC ID NSF Approved CA T20 / T24 Rationale California Status Title 20 / 24 Status California Prop 65	Wet No Yes S-U80D4A Yes T20 Exempt - Fixtures Not Regulated Lawful for sale in California Lawful for sale
Location Rating Energy Star DLC Approved DLC ID NSF Approved CA T20 / T24 Rationale California Status Title 20 / 24 Status California Prop 65 RoHS Compliant	Wet No Yes S-U80D4A Yes T20 Exempt - Fixtures Not Regulated Lawful for sale in California Lawful for sale Lead
Location Rating Energy Star DLC Approved DLC ID NSF Approved CA T20 / T24 Rationale California Status	Wet No Yes S-U80D4A Yes T20 Exempt - Fixtures Not Regulated Lawful for sale in California Lawful for sale Lead Yes
Location Rating Energy Star DLC Approved DLC ID NSF Approved CA T20 / T24 Rationale California Status Title 20 / 24 Status California Prop 65 RoHS Compliant FCC Compliant	Wet No Yes S-U80D4A Yes T20 Exempt - Fixtures Not Regulated Lawful for sale in California Lawful for sale Lead Yes Yes
Location Rating Energy Star DLC Approved DLC ID NSF Approved CA T20 / T24 Rationale California Status Title 20 / 24 Status California Prop 65 RoHS Compliant FCC Compliant SDS Sheet	Wet No Yes S-U80D4A Yes T20 Exempt - Fixtures Not Regulated Lawful for sale in California Lawful for sale Lead Yes Yes
Location Rating Energy Star DLC Approved DLC ID NSF Approved CA T20 / T24 Rationale California Status Title 20 / 24 Status California Prop 65 RoHS Compliant FCC Compliant SDS Sheet Additional Information	Wet No Yes S-U80D4A Yes T20 Exempt - Fixtures Not Regulated Lawful for sale in California Lawful for sale Lead Yes Yes Lead Yes LED_Fixture