

## Easy thread design and control panel



- **Powered pre-stretch @ 225%**
- **4,000lb load capacity**
- **Photo eye seeks pallet load height**
- **Turntable will automatically return to home position**
- **“Easy thread design”**
- **7” HMI touch screen with programmable memory**
- **110V**
- **Turntable speed 0-15RPM**
- **Optional features**
  - **72” diameter turntable**
  - **Tower extensions to 105”**
  - **Base extension**
  - **Insta-cut automatic film severance**
  - **Weight scale packages**

### More Details:

SPW-983HP is a high profile model that can be loaded by forklift only. Ramp not included.  
 SPW-983LP is a low profile model that can be loaded by forklift or pallet jack.

### Specifications:

PRODUCTION RATE	30 – 40 LPH	MACHINE DIMENSIONS	108”L X 59”W X 102”H
POWER REQUIREMENTS	110 VOLTS, 1 PHASE, 15 AMP	CARRIAGE ELEVATOR	VARIABLE SPEED ½ HP – DRIVE BELT
MAXIMUM LOAD SIZE	50”L X 50”W x 85”H	CONTROL	PLC CONTROL W/ 12 PROGRAM MEMORY
MAXIMUM LOAD	4,000-LBS	FORK LIFT PORTABLE	YES
TURNTABLE	59” DIAMETER – 3/8” DIAMOND PLATE	CE APPROVAL	EXCEEDS OSHA SAFETY STANDARDS
TURNTABLE DRIVE	½ HP AC VARIABLE SPEED 0-15 RPM	PHOTO EYE	WILL SEAK HEIGHT OF PALLET LOAD
TURNTABLE DRIVE METHOD	HEAVY DUTY CHAIN ANSI #60	SHIPPING WEIGHT & DIMENSIONS	1,850-LBS 120” X 66” X 30”
TURNTABLE SUPPORT	HEAVY DUTY DELRIN DOUBLE RING ROLLER ASSEMBLY	FILM CAPACITY	ALL COMMERCIAL 20” WIDE STRETCH FILM
FILM DELIVERY SYSTEMS	PATENTED TRIPLE KNURLED ROLLER WITH “EASY THREAD DESIGN” TO STRETCH FILM 225%	WARRANTY	3 YEAR LIMITED WARRANTY

# STRETCH PALLET WRAPPER

Model: *SPW-983HP | SPW-983LP*



- HMI touch screen
- PLC control with 12 program memory
  - On/off switch
  - Top wrap count
  - Bottom wrap count
  - Start / stop
  - Manual / automatic
  - Pause button
  - Film tension control
  - Turntable speed
  - Film carriage speed
  - Emergency stop switch




Patented triple knurled roller pre-stretch system with 225% powered pre-stretch. Easy thread design with safety door; if opened, machine will shut off



SPW-983LP  
Low Profile



SPW-983HP  
High Profile  
Does not include ramp



Heavy duty chain drive on turntable with 18sets of double roller turntable supports.