

29 142

GROHTHERM® SMARTCONTROL

TRIPLE FUNCTION THERMOSTATIC VALVE TRIM WITH CONTROL MODULE

Pure Freude
an Wasser



STANDARD SPECIFICATION:

- GROHE StarLight®
- GROHE SmartControl®: push for ON-OFF, turn for volume adjustment from EcoJoy™ to Full Flow, exchangeable symbols
- GROHE TurboStat® compact 3/4" cartridge with wax thermo element
- GROHE SafeStop safety button with manual override at 100°F/38°C
- GROHE SafeStop Plus temperature limiter at 115° F/46° C
- Multiple outlets can be run simultaneously
- 6 1/4" Metal wall escutcheon with GROHE QuickFix®
- 3/8" Thin profile escutcheon
- Wall plate is angle adjustable up to 6°
- Optional flow reducer for CALGreen compliance included (Note: Cannot be used for shower systems that include tub spout)
- Built-in check valve with dirt strainer
- Includes icons to customize push buttons: Hand Shower, Showerhead, Bath Filler, Showerhead (2nd Spray), Showerhead (3rd Spray) & Body Spray
- Includes service stops
- Maximum combined flow performance: 9.5gpm (36L/min) @ 43.5psi (3 bar)
- Requires Grotherm® Rapido® SmartBox (35 601) (sold separately)



PRODUCT FEATURES:

- GROHE StarLight®
- GROHE TurboStat®
- GROHE QuickFix®
- GROHE SmartControl®
- GROHE SafeStopPlus

CERTIFICATIONS:

- Massachusetts Plumbing Board Approved
- ASSE 1016
- CSA B125.1
- CSA B125.16
- ASME A112.18.1
- ASME A112.1016

AVAILABLE FINISHES:

- 29142000** GROHE StarLight® Chrome
- 29142A00** Hard Graphite
- 29142EN0** Brushed Nickel InfinityFinish™
- 29142GN0** Brushed Cool Sunrise

NOTE: Install this product according to the installation guide. ADA, CSA compliant when installed to the specific requirements of these regulations.

We reserve the right to make revisions without notice to product specifications. 07-06-2022

US
Tel: 1.630.582.7711 Fax: 1.630.582.7722
For the most current Specification Sheet,
go to www.grohe.us.

Canada
Tel: 1.888.644.7643 Fax: 1.905.366.2071
For the most current Specification Sheet,
go to www.grohe.ca.

PART OF **LIXIL**

29 142

GROHTHERM® SMARTCONTROL

TRIPLE FUNCTION THERMOSTATIC VALVE TRIM WITH CONTROL MODULE

Pure Freude
an Wasser



TECHNICAL DATA:

Product Height	6-1/4 in
Product Length	1-11/16 in
Product Width	6-1/4 in

