


PLASTIC PALLET/SKID - PLPG-4848-HD




APPROX WEIGHT: 66 lbs.
 DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***
 ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



PALLET IS DOUBLE SIDED
 (BOTTOM IS SAME AS TOP)
 NO OPENINGS ON BOTTOM,
 MAY NOT BE LIFTED WITH
 A PALLET JACK

HOLE PATTERN MAY VARY



STANDARD FEATURES

- MODEL NUMBER IS PLPG-4848-HD
- OVERALL WIDTH IS 47 1/4"
- OVERALL LENGTH IS 47 1/4"
- OVERALL HEIGHT IS 5 11/16"
- INJECTION MOLDED, MATERIAL IS HIGH DENSITY POLYETHYLENE
- RACKABLE (FOR USE ON PALLET RACKS)
- STACKABLE FOR EFFICIENT STORAGE
- FLOOR (STATIC) WEIGHT CAPACITY IS 22,000 LBS.
- FORK (DYNAMIC) WEIGHT CAPACITY IS 3,900 LBS.
- UNSUPPORTED PALLET RACK WEIGHT CAPACITY IS 1,600 LBS.
- FORK OPENINGS (W X H) ARE 12 1/4" X 3 1/2"
- PALLET WEIGHT IS 66 LBS. APPROX.
- BLACK IN COLOR

SPECIAL FEATURES

NONE

A P P R O V A L	I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.	
	UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE	
	[] As drawn [] As marked	
Signed: _____		Date: _____
Printed Name: _____		
<i>LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING</i>		

DISTRIBUTOR'S NAME:		P.O.#
VESTIL MANUFACTURING		X
DRAWN BY: DEY		W.O.#
DATE: 12/30/10		X
REFERENCE: X	SCALE: 1:24	SALES: X
QUOTED LEAD TIME: X	QUOTE #	FILE NAME:
	X	PLPG-4848-HD