


SELF-DUMPING STEEL HOPPER W/ BUMPER RELEASE - D-250-LD APPROX WEIGHT: 864.22 lbs.

DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***

ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES

MODEL NUMBER: D-250-LD
 VOLUME: 2 1/2 CU. YDS.
 CAPACITY: 2,000 LBS.
 OVERALL WIDTH: 69 9/16"
 OVERALL LENGTH: 68 3/8"
 OVERALL HEIGHT: 51 3/4"
 PULL CABLE IS AT LEAST: 48"
 TOUGH BAKED IN POWDER
 COATED BLUE FINISH

SPECIAL FEATURES

NONE

NEVER EXCEED LOAD CENTER RATING PER FORK
 TRUCK MANUFACTURER'S GUIDELINES.
 DO NOT USE THIS FORK TRUCK ATTACHMENT IF
 LOAD WILL EXCEED FORK TRUCK
 MANUFACTURER'S LOAD CENTER RATING.
 APPROX. WEIGHT/ LOST LOAD=864.22 LBS.
 MINIMUM EFFECTIVE THICKNESS= LESS THAN 1"

APPROVAL

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS
 REPRESENTED SATISFIES DESIGN AND DIMENSION
 REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO
 CONFIRM PRODUCT AND INSTALLATION
 COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE
 AND LOCAL REGULATIONS AND STANDARDS.
**UNITS REQUIRING APPROVAL DRAWINGS OR
 MODIFIED ARE NON-RETURNABLE**
 As drawn As marked

Signed: _____ Date: _____

Printed Name: _____

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

DISTRIBUTOR'S NAME:		P.O.#
VESTIL MANUFACTURING		X
DRAWN BY: W.STALEY		W.O.#
DATE: 5/7/08		X
REFERENCE: X	SCALE: 1:22	SALES: X
QUOTED LEAD TIME: X	QUOTE #	FILE NAME:
	X	37-007-056

ADDITION OF CASTERS MAY CHANGE WEIGHT CAPACITY BASED ON CASTER RATING