

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0351510310](#)  
**Status:** **Active**  
**Overview:** [VersaBlade Wire-to-Wire Connector System](#)  
**Description:** [VersaBlade Hybrid Plug Housing, 3 Circuits, Positive Lock, Natural](#)

**Documents:**

<a href="#">3D Model (PDF)</a>	<a href="#">Application Specification 351500000ASKOR-000 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-35151-004-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification PS-35150-001-001 (PDF)</a>	<a href="#">Brochure (PDF)</a>
<a href="#">Product Specification PS-35150-003-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification 351500000ASENG-000 (PDF)</a>	

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	Crimp Housings
Series	<a href="#">35151</a>
Application	Power, Wire-to-Wire
Overview	<a href="#">VersaBlade Wire-to-Wire Connector System</a>
Product Name	VersaBlade
Taxonomy	Connector Housings
UPC	800753876811

**Physical**

Circuits (maximum)	3
Color - Resin	Natural
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	3.133/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	7.30mm
Pitch - Termination Interface	7.30mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +120°C

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Application Specification	351500000AS_ENG-000, 351500000AS_KOR-000
Packaging Specification	PK-35151-004-001
Product Specification	PS-35150-001-001, PS-35150-003-001
Sales Drawing	SD-35151-031-001, SD-35151-031X-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[35151](#) Series

**Mates With**

VersaBlade Receptacle Housing [35150](#)  
<br>VersaBlade Multi-Module 2-3-4  
Receptacle Housing [35524](#) , [2026500909](#)

**Use With**

VersaBlade Crimp Terminals [35746](#) (ckt 1),  
[35745](#) (ckt 2), [35748](#) (ckt 3) <br>VersaBlade  
TPA [351500390](#) , [351500392](#) , [351500393](#) ,  
[351500394](#)

This document was generated on 08/30/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**