

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1203410601](#)
Status: **Active**
Overview: [Brad Industrial Ethernet Solutions](#)
Description: Standard RJ-45 CAT6A Double-Ended Cordset, 8 Poles, Male (Straight) to Male (Straight), 26 AWG, Teal Shielded PUR Cable, 1.0m (3.28') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-120341-600-001 \(PDF\)](#)

Agency Certification

UL E361772

General

Product Family Industrial Cordsets
 Series [120341](#)
 Connector End A RJ-45 (standard)
 Connector End B RJ-45 (standard)
 IP Rating IP20
 Material - Contact Brass
 Overview [Brad Industrial Ethernet Solutions](#)
 Performance Category 6A
 Product Name Industrial Ethernet
 Region America, Asia, Europe
 Taxonomy Circular Industrial Cordsets
 Type Double Ended
 UPC 887191679020

Physical

Cable Diameter 6.40mm (.252")
 Cable Length 1.0m (3.28')
 Color - Cable Jacket Teal
 Coupling Style Threaded
 Gender Male-Male
 Keyway N/A
 LED Indicator No
 Material - Cable Jacket PUR
 Material - Connector Body PUR
 Material - Coupling Nut N/A
 Material - Plating Mating Gold
 Net Weight 62.800/g
 Orientation Straight to Straight
 Poles 8
 Temperature Range - Operating -40° to +70°C
 Wire Size AWG 26
 Wire/Cable Type Shielded PUR

Electrical

Current - Maximum per Contact 0.5A
 Voltage - Maximum 30V AC / 60V DC

Material Info

Engineering Number E66E06020M010

Reference - Drawing Numbers

Packaging Specification PK-120341-600-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/01/2018 (15
 January 2018)

Halogen-Free

Status

Low-Halogen*

For more information, please visit [Contact US](#)

CUST_NOTE	*Product contains part(s) with customer managed
CUST_NOTE1	EHS data. These part(s) are excluded from product compliance status evaluation.
CUST_NOTE2	Green Image
China ROHS	Not Relevant
ELV	Not Contained
RoHS Phthalates	CER_4000410546_00_000.pdf
ZZCERT_UKCA	- Declaration of Conformity

Search Parts in this Series

[120341 Series](#)

Mates With

[120341 Micro-Change CAT6A Receptacles](#)

This document was generated on 10/18/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION