

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0016020087](#)
Status: **Active**
Overview: SL Modular Connectors
Description: SL Crimp Terminal, Series 70058, Female, 22-24 AWG, with 0.38µm Selective Gold (Au) Plated Contact, Reel

Documents:

[Drawing \(PDF\)](#) [Test Summary TS-70058-001-001 \(PDF\)](#)
[Product Specification PS-70058-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-70400-001 \(PDF\)](#)

General

Product Family Crimp Terminals
 Series [70058](#)
 Application Signal, Wire-to-Board, Wire-to-Wire
 Crimp Quality Equipment Yes
 Overview [SL Modular Connectors](#)
 Packaging Alternative [16020103 \(Bag\)](#)
 Product Name CyClone, SL
 Taxonomy Crimp Terminals
 UPC 800753596023

Physical

Gender Female
 Material - Metal Phosphor Bronze
 Material - Plating Mating Gold
 Material - Plating Termination Tin
 Net Weight 0.073/g
 Packaging Type Reel
 Plating min - Mating 0.380µm
 Plating min - Termination 2.000µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 1.63mm max.
 Wire Size AWG 22, 24
 Wire Size mm² N/A

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number 70058-0024

Reference - Drawing Numbers

Product Specification PS-70058-001, PS-70400-001
 Sales Drawing 700580001-SD-000
 Test Summary TS-70058-001-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2022)4187-DC (10
 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[70058 Series](#)

Use With

SL Crimp Housing [70066](#) , [70450](#)

CyClone Connector [73099](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description **Product #**

Insertion Tool for [11020022](#)
 70021,70028, 70110,
 71851 Terminals /
 Extraction Tool for
 91821 Terminals
 PremiumGrade Hand[638118700](#)
 Crimp Tool for SL
 Crimp Terminals,
 22-24 AWG and
 32-36 AWG

FineAdjust Applicator 639023200
for SL Crimp
Terminals, for 22-24
AWG Wire with
Insulation Diameter
1.40-1.63mm
T2 Terminator 639123200
for Female Crimp
Terminal

This document was generated on 10/31/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION