

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0638112600](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** PremiumGrade Hand Crimp Tool for 1.50mm MX150 Blade Male Terminals, 18-22 AWG

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Application Tooling
Series	<a href="#">207129</a>
Comments	Prototype and field repair; Type: 4A
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	N/A
Taxonomy	Crimp Presses and Crimp Hand T
Tool Type	Hand Crimp Tool
UPC	756054649695
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.


**Physical**

Net Weight 428.885/g

**Material Info**

**Reference - Drawing Numbers**

Application Tooling Documents  
 ATS-6381126HM-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/61/2018 (27 June 2018)

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Not Relevant

Not Relevant

Not Contained

**Search Parts in this Series**

[207129](#) Series

**Use With**

Loose Piece Terminals

**Application Tooling**

**Description**

**FAQ**

**Product #**

MX150 Male [312960008](#)

Terminal for Mat-Sealed Connectors with Shorting Bars, Gold (Au) Plating, 18-20 AWG, Left to Right Reel Payoff

MX150 Male [312961008](#)

Terminal for Mat-Sealed Connectors with Shorting Bars, Gold (Au) Plating, 18-20 AWG, Right to Left Reel Payoff

MX150 Male [330000002](#)

Terminal for Mat-Sealed or Unsealed Connectors, Tin

Plating, 16, 18 and  
20 AWG, Right Reel  
Payoff

MX150 Male 330000003

Terminal for Mat-  
Sealed or Unsealed  
Connectors, Tin  
Plating, 22 AWG,  
Right Reel Payoff

MX150 Male 330001002

Terminal for Mat-  
Sealed or Unsealed  
Connectors, Tin  
Plating, 16, 18 and  
20 AWG, Left Reel  
Payoff

MX150 Male 330001003

Terminal for Mat-  
Sealed or Unsealed  
Connectors, Tin  
Plating, 22 AWG,  
Left Reel Payoff

MX150 Male 330110002

Terminal for Mat-  
Sealed or Unsealed  
Connectors, Gold  
Plating, 14 AWG,  
Left Reel Payoff

MX150 Male 330110004

Terminal for Mat-  
Sealed or Unsealed  
Connectors, Gold  
Plating, 16, 18 and  
20 AWG, Left Reel  
Payoff

MX150 Male 330110006

Terminal for Mat-  
Sealed or Unsealed  
Connectors, Gold  
Plating, 22 AWG,  
Left Reel Payoff

MX150 Male 330111002

Terminal for Mat-  
Sealed or Unsealed  
Connectors, Gold  
Plating, 14 AWG,  
Right Reel Payoff

MX150 Male 330111004

Terminal for Mat-  
Sealed or Unsealed  
Connectors, Gold  
Plating, 16, 18 and  
20 AWG, Right Reel  
Payoff

MX150 Male 330111006

Terminal for Mat-  
Sealed or Unsealed  
Connectors, Gold  
Plating, 22 AWG,  
Right Reel Payoff

MX150 Male 330112001

Terminal for Mat-  
Sealed or Unsealed  
Connectors, Silver

Plating, 22 AWG, Right Reel Payoff MX150 Male	<u>330112002</u>
Terminal for Mat- Sealed or Unsealed Connectors, Silver Plating, 16, 18 and 20 AWG, Right Reel Payoff MX150 Male	<u>330113001</u>
Terminal for Mat- Sealed or Unsealed Connectors, Silver Plating, 22 AWG, Left Reel Payoff MX150 Male	<u>330113002</u>
Terminal for Mat- Sealed or Unsealed Connectors, Silver Plating, 16, 18 and 20 AWG, Left Reel Payoff	

This document was generated on 10/12/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**