

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300840132](#)  
**Status:** **Active**  
**Overview:** [Reels - Woodhead](#)  
**Description:** Woodhead POW-R-MITE Heavy Duty Cable Reel with Retraction Weight of 4lbs., 12/3 SOW, 21.34m (70.0') Cord Length with Flying Leads

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR29921

**General**

Product Family Electric Reels  
 Series [130084](#)  
 Cable Length N/A  
 Comments Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.  
 Depth 0.48m (19.00")  
 Duty Heavy  
 Enclosure Rating NEMA 3  
 Height 0.52m (20.50")  
 NEMA Configuration N/A  
 Overview [Reels - Woodhead](#)  
 Product Name POW-R-MITE  
 Taxonomy Electric Reels  
 Type Cable Reel  
 UPC 78678827475  
 Width 423.42mm (16.670")

**Physical**

Cable Movement Ratchet Lock  
 Cord Length 21.34m (70.0')  
 Drum Lock Ratchet  
 Guide Arm 4 - Postion  
 Material - Coating Powder Coating  
 Material - Housing Steel  
 Mounting Style Rigid  
 Net Weight 72574.720/g  
 Number of Conductors 3  
 Packaging Type Carton  
 Primary Cord/Cable Entry 1" NPT  
 Retraction Weight 1.8kg (4.0 lb)  
 Wire Size AWG 12

**Electrical**

Bulb Included N/A  
 Cord Type 12/3 SOW  
 Current - Maximum per Contact 20.0A  
 GFCI No  
 Lamp Type N/A  
 Lamp Wattage - Maximum N/A  
 On/Off Switch N/A  
 Voltage - Maximum 600V

**Material Info**

Engineering Number 92533N



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130084 Series](#)

This document was generated on 10/13/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**